



Eaton 290171

Eaton Distribution parts. Restarting device-set, 220-240VAC, 6HP

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	290171
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	77.3 mm
PRODUCT WIDTH	123.4 mm
PRODUCT WEIGHT	0.375 kg
COMPLIANCES	RoHS conform

USED WITH

Restarting device - pre-assembled kits
 Accessory for residual current circuit breaker
 Accessory
 Accessory for miniature circuit breaker

ACCESSORY/SPARE PART TYPE

Restarting device

EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT

0 W

MOUNTING METHOD

For fitting on right to:
 CLS6, PFIM, PFHM-4p,
 dRCM, Z-A40, PFR, Z-MS

ADDITIONAL EQUIPMENT REQUIRED

Monitoring unit with automatic reclosing

AMBIENT OPERATING TEMPERATURE - MAX

40 °C

AMBIENT OPERATING TEMPERATURE - MIN

-25 °C

ASSEMBLY WIDTH

6 TE

HEAT DISSIPATION CAPACITY

0 W

HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT

0 W

NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)

0

NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)

0

NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)

0

NUMBER OF POLES AT MAIN CONTACT UNIT - MAX

0

NUMBER OF SWITCHES (FAULT SIGNAL)

0

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)

0 A

VOLTAGE TYPE

AC

FUNCTIONS

With auto test for earth leakage function
 Monitoring unit with automatic reclosing

DEVICE FITTING

Universal

[eaton-dimensions-mas-hk.jpg](#)

TYPE	<ul style="list-style-type: none">• Accessory• Accessory for miniature circuit breaker• Accessory for residual current circuit breaker
APPLICATION	Switchgear for industrial and advanced commercial applications
RATED OPERATIONAL VOLTAGE (UE) - MAX	230 V
RATED SWITCH CURRENT	0 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	3.5 W
SUITABLE FOR CURRENT OF MAIN CONTACT UNIT - MAX	0 A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:

