



□□□□□

## Eaton 278774

Eaton Moeller series xEffect - FAZ MCB. FAZ, 2-pole, tripping characteristic: D, rated current In: 3.5 A

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xEffect - FAZ MCB
<b>CATALOG NUMBER</b>	278774
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	75.5 mm
<b>PRODUCT WIDTH</b>	36 mm
<b>PRODUCT WEIGHT</b>	0.225 kg
<b>COMPLIANCES</b>	UL CSA09 (with supplementary protector only) RoHS conform
<b>CERTIFICATIONS</b>	UL 1077 CSA (Class No. 3215-30) UL (Category Control Number QVNU2, QVNU8) IEC/EN 60947-2 CSA (File No. 204453) North America (UL recognized, CSA certified) UL (File No. E177451) CE marking CSA-C22.2 No. 235 IEC/EN 60898 EN45545-2 IEC 61373

## □□□□

<b>USED WITH</b>	FAZ Miniature circuit breaker
<b>AMPERAGE RATING</b>	3.5 A
<b>VOLTAGE RATING</b>	240 V AC / 415 V AC
<b>FEATURES</b>	Additional equipment possible
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.

## □□

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-xeffect-faz-mcb-characteristic-curve.jpg</a>
<b>□□□</b>	<a href="#">eaton-mcb-xeffect-faz-wiring-diagram-002.eps</a> <a href="#">eaton-xpole-mmc4-6-m-mcb-wiring-diagram-003.jpg</a>
<b>□□</b>	<a href="#">eaton-xeffect-faz-mcb-dimensions-002.jpg</a> <a href="#">eaton-xeffect-faz-mcb-3d-drawing-003.jpg</a> <a href="#">eaton-mcb-faz-xeffect-faz-3d-drawing-002.eps</a> <a href="#">eaton-xeffect-faz-mcb-3d-drawing-012.jpg</a> <a href="#">eaton-xeffect-faz-mcb-3d-drawing-011.jpg</a>

<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>POLLUTION DEGREE</b>	2
<b>DEGREE OF PROTECTION</b>	IP20 (IEC) UL/CSA Type: - IP20
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	2.6 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV
<b>TRIPPING CHARACTERISTIC</b>	D
<b>VOLTAGE RATING (UL CSA 13)</b>	480 Y/277 V AC; 96 V DC
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1 mm <sup>2</sup>

<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	25 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1 mm <sup>2</sup>
<b>CURRENT LIMITING CLASS</b>	3
<b>FREQUENCY RATING - MAX</b>	60 Hz
<b>FREQUENCY RATING - MIN</b>	50 Hz
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT</b>	0 W
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	2
<b>VOLTAGE TYPE</b>	AC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>NUMBER OF POLES</b>	Two-pole
<b>RELEASE CHARACTERISTIC</b>	D
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• FAZ</li> <li>• Miniature circuit breaker</li> </ul>
<b>SPECIAL FEATURES</b>	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• Branch circuits, not as BCPD</li> <li>• Switchgear for industrial and advanced commercial applications</li> <li>• xEffect - Switchgear for industrial and advanced commercial applications</li> </ul>
<b>NUMBER OF POLES (PROTECTED)</b>	2
<b>NUMBER OF POLES (TOTAL)</b>	2

RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	3.5 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	15 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V	15 kA
RATED SWITCHING CAPACITY (IEC/EN 60947-2)	15 kA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
POWER LOSS	2.6 W
