



□□□□□

Eaton 278881

Eaton Moeller series xEffect - FAZ MCB. FAZ, 3-pole, tripping characteristic: D, rated current In: 1 A

□□□□

PRODUCT NAME	Eaton Moeller series xEffect - FAZ MCB
CATALOG NUMBER	278881
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	0.335 kg
COMPLIANCES	UL CSA09 (with supplementary protector only) RoHS conform
CERTIFICATIONS	IEC/EN 60898 CSA (Class No. 3215-30) CSA-C22.2 No. 235 IEC/EN 60947-2 CSA (File No. 204453) UL (File No. E177451) North America (UL recognized, CSA certified) CE marking UL 1077 UL (Category Control Number QVNU2, QVNU8) EN45545-2 IEC 61373

□□□□

USED WITH	Miniature circuit breaker FAZ
AMPERAGE RATING	1 A
VOLTAGE RATING	240 V AC / 415 V AC
FEATURES	Additional equipment possible
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

CHARACTERISTIC CURVE	eaton-xeffect-faz-mcb-characteristic-curve.jpg
□□□	eaton-xpole-mmc4-6-m-mcb-wiring-diagram-005.jpg
	eaton-xeffect-faz-mcb-dimensions-003.jpg
	eaton-xeffect-faz-mcb-3d-drawing-011.jpg
□□	eaton-xeffect-faz-mcb-3d-drawing-003.jpg
	eaton-xeffect-faz-mcb-3d-drawing-012.jpg
	eaton-mcb-faz-xeffect-faz-3d-drawing-003.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20 IP20 (IEC) UL/CSA Type: -
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	2.4 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
TRIPPING CHARACTERISTIC	D
VOLTAGE RATING (UL CSA 13)	480 Y/277 V AC
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²

CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT	0 W
WIDTH IN NUMBER OF MODULAR SPACINGS	3
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Three-pole
RELEASE CHARACTERISTIC	D
TYPE	<ul style="list-style-type: none"> • FAZ • Miniature circuit breaker
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	<ul style="list-style-type: none"> • Branch circuits, not as BCPD • Switchgear for industrial and advanced commercial applications • xEffect - Switchgear for industrial and advanced commercial applications
NUMBER OF POLES (PROTECTED)	3
NUMBER OF POLES (TOTAL)	3

RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	1 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	15 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V	15 kA
RATED SWITCHING CAPACITY (IEC/EN 60947-2)	15 kA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
POWER LOSS	2.4 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

