



□□□□

## Eaton 3-5001-005A

Eaton DM1 Variable frequency drive, 240 V AC, 3-phase, 2.1 A, IP20, NEMA Other, FS1, Radio interference, Brake chopper, Digital display

□□□□

<b>PRODUCT NAME</b>	Eaton DM1 Variable frequency drive
<b>CATALOG NUMBER</b>	3-5001-005A
<b>PRODUCT LENGTH/DEPTH</b>	180 mm
<b>PRODUCT HEIGHT</b>	152 mm
<b>PRODUCT WIDTH</b>	72 mm
<b>PRODUCT WEIGHT</b>	1.2 kg
<b>CERTIFICATIONS</b>	IEC/EN 61800-5-1 UL 508C CSA-C22.2 No. 274-13 EAC UL UL Listed UL report applies to both US and Canada C-Tick CSA-C22.2 No. 274-17 UkrSEPRO UL File No.: E134360 RoHS, ISO 9001 CUL UL Category Control No.: NMMS, NMMS7 Certified by UL for use in Canada CE IEC/EN 61800-3 CE marking IEC/EN61800-3 IEC/EN61800-5 IEC/EN 61800-2



Powering Business Worldwide

<b>PRODUCT CATEGORY</b>	Variable frequency drives
<b>FEATURES</b>	Temperature-controlled fan Parameterization: Keypad Parameterization: Fieldbus  Parameterization: Power Xpert inControl
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.

	<a href="#">fs1-89-1309.stp</a>
MCAD MODEL	<a href="#">eaton-general-purpose-drives-mcad-drawings-fs1-89-1309.dwg</a>
□□□□	<a href="#">eaton-variable-frequency-drive-dm1-application-manual-mn040049-en-us.pdf</a>

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Setpoint potentiometer IGBT inverter Internal DC link Radio interference suppression filter 7-digital display assembly Brake chopper Control unit PC connection
<b>POLLUTION DEGREE</b>	2
<b>CLIMATIC PROOFING</b>	< 95 average relative humidity (RH), no condensation, no corrosion
<b>CONNECTION TO SMARTWIRE-DT</b>	Yes In conjunction with DXG-NET-SWD SmartWire DT module
<b>OPERATING MODE</b>	Speed control with slip compensation Sensorless vector control (SLV) PM motors Torque regulation U/f control
<b>FRAME SIZE</b>	FS1
<b>AIR VOLUME CAPACITY</b>	26 m <sup>3</sup> /h

<b>ALTITUDE</b>	Max. 2000 m for Corner Grounded TN Systems Max. 1000 m Max. 3000 m Above 1000 m with 1 % derating per 100 m
<b>ENVIRONMENTAL CLASS</b>	3C2, 3S2 (Air quality)
<b>APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED</b>	Yes
<b>MAINS SWITCH-ON FREQUENCY</b>	Maximum of one time every 60 seconds
<b>APPLICATION IN INDUSTRIAL AREA PERMITTED</b>	Yes
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>ASSIGNED MOTOR CURRENT IM AT 230 V, 50 HZ, 150% OVERLOAD</b>	1.4 A
<b>MAINS VOLTAGE TOLERANCE</b>	200 - 240 V (-15 %/+10 %, at 50/60 Hz)
<b>MOUNTING POSITION</b>	Vertical
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	100 kA
<b>RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE</b>	10 %
<b>RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE</b>	10 %
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
<b>RESOLUTION</b>	0.01 Hz (Frequency resolution, setpoint value)
<b>VOLTAGE RATING - MAX</b>	240 V
<b>OVERVOLTAGE CATEGORY</b>	III
<b>COMMUNICATION INTERFACE</b>	DeviceNet, optional Ethernet IP, built in Modbus RTU, built in Modbus TCP, built in

	SmartWire-DT, optional PROFIBUS, optional BACnet MS/TP, built in BACnet TCP CANopen®, optional
<b>CONVERTER TYPE</b>	U converter
<b>DEGREE OF PROTECTION</b>	IP20 NEMA Other
<b>PROTOCOL</b>	BACnet CAN EtherNet/IP MODBUS Other bus systems PROFIBUS TCP/IP
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE</b>	0.25 HP
<b>SYSTEM CONFIGURATION TYPE</b>	TN-S, TN-C, TN-C-S, TT, IT
<b>ELECTROMAGNETIC COMPATIBILITY</b>	1st and 2nd environments (according to EN 61800-3)
<b>ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE, 110 % OVERLOAD</b>	0.5 HP
<b>BRAKING RESISTANCE</b>	36 Ω
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	33 W
<b>INPUT CURRENT ILN AT 110% OVERLOAD</b>	3.3 A
<b>INPUT CURRENT ILN AT 150% OVERLOAD</b>	2.1 A
<b>MAINS CURRENT DISTORTION</b>	40 %
<b>CURRENT LIMITATION</b>	0.1 - 2 x IH (CT), motor, main circuit
<b>NUMBER OF SLOTS</b>	1 (expansion)
<b>BRAKING TORQUE</b>	Max. 100 % of rated operational current I <sub>e</sub> with external braking resistor - Main circuit Adjustable to 150 %, DC - Main circuit Max. 30 % MN, Standard - Main circuit
<b>CABLE LENGTH</b>	C2 ≤ 5 m, maximum motor cable length C3 ≤ 25 m, maximum motor cable length
<b>FUNCTIONS</b>	4-quadrant operation possible

<b>OUTPUT VOLTAGE (U2)</b>	240 V AC, 3-phase 230 V AC, 3-phase
<b>NUMBER OF INPUTS (ANALOG)</b>	1
<b>NUMBER OF INPUTS (DIGITAL)</b>	4
<b>RADIO INTERFERENCE CLASS</b>	Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: with external filter
<b>NUMBER OF OUTPUTS (DIGITAL)</b>	0
<b>STARTING CURRENT - MAX</b>	200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
<b>NUMBER OF PHASES (INPUT)</b>	3
<b>NUMBER OF RELAY OUTPUTS</b>	2 (parameterizable, 1 changeover contact and 1 N/O, 3 A (240 V AC) / 3 A (24 V DC))
<b>NUMBER OF PHASES (OUTPUT)</b>	3
<b>POWER CONSUMPTION</b>	33 W
<b>RATED CONTROL SUPPLY VOLTAGE</b>	10 V DC (Us, max. 10 mA)
<b>RATED CONTROL VOLTAGE (UC)</b>	24 V DC (external, max. 100 mA options incl.)
<b>SUPPLY FREQUENCY</b>	50/60 Hz
<b>MAINS VOLTAGE - MAX</b>	240 V
<b>MAINS VOLTAGE - MIN</b>	200 V
<b>NOMINAL OUTPUT CURRENT I2N</b>	1.6 A
<b>NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)</b>	1
<b>NUMBER OF HW-INTERFACES (OTHER)</b>	1
<b>NUMBER OF HW-INTERFACES (PARALLEL)</b>	0

<b>NUMBER OF HW-INTERFACES (RS-232)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-422)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-485)</b>	1
<b>NUMBER OF HW-INTERFACES (SERIAL TTY)</b>	0
<b>NUMBER OF HW-INTERFACES (USB)</b>	0
<b>NUMBER OF INTERFACES (PROFINET)</b>	0
<b>NUMBER OF OUTPUTS (ANALOG)</b>	1
<b>OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	0.18 kW
<b>OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	0.37 kW
<b>OUTPUT FREQUENCY - MAX</b>	400 Hz
<b>OUTPUT FREQUENCY - MIN</b>	0 Hz
<b>OUTPUT VOLTAGE - MAX</b>	240 V
<b>OVERLOAD CURRENT I<sub>L</sub> AT 110% OVERLOAD</b>	3.3 A
<b>OVERLOAD CURRENT I<sub>L</sub> AT 150% OVERLOAD</b>	2.4 A
<b>SHOCK RESISTANCE</b>	0.75 mm (peak) at 10 - 57 Hz, max. 1 g at 57 - 150 Hz, according to EN 61800-5-1, EN 60068-2-6: 10 - 150 Hz
<b>SUITABLE FOR</b>	Branch circuits, (UL/CSA)
<b>SWITCHING FREQUENCY</b>	4 kHz, 1 - 16 kHz adjustable, fPWM, Power section, Main circuit
<b>RATED OPERATIONAL VOLTAGE</b>	230 V AC, 3-phase 240 V AC, 3-phase
<b>SHORT-CIRCUIT PROTECTION RATING</b>	4 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
<b>RATED FREQUENCY - MAX</b>	66 Hz
<b>RATED FREQUENCY - MIN</b>	45 Hz
<b>RATED OPERATIONAL CURRENT (I<sub>E</sub>) AT 110% OVERLOAD</b>	3 A
<b>RATED OPERATIONAL CURRENT (I<sub>E</sub>) AT 150%</b>	1.6 A

