



□□□□□

Eaton 279028

Eaton Moeller series xEffect - FAZ MCB. FAZ, 4 pole, tripping characteristic: B, rated current In: 5 A

□□□□

PRODUCT NAME	Eaton Moeller series xEffect - FAZ MCB
CATALOG NUMBER	279028
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	72 mm
PRODUCT WEIGHT	0.446 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	EN45545-2 IEC 61373

□□□□

USED WITH	Miniature circuit breaker FAZ
AMPERAGE RATING	5 A
FEATURES	Additional equipment possible
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

□□

CHARACTERISTIC CURVE	eaton-xeffect-faz-mcb-characteristic-curve.jpg
□□□	eaton-xpole-mmc4-6-mcb-wiring-diagram-006.jpg
□□	eaton-xeffect-faz-mcb-dimensions-004.jpg eaton-xeffect-faz-mcb-3d-drawing-008.jpg eaton-xeffect-faz-mcb-3d-drawing.jpg eaton-xeffect-faz-mcb-3d-drawing-007.jpg

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	7.6 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
BREAKING CAPACITY	10 kA (UL1077)
TRIPPING CHARACTERISTIC	B
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²

CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
VOLTAGE RATING (IEC/EN 60898-1)	415 VAC
WIDTH IN NUMBER OF MODULAR SPACINGS	4
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Four-pole
RELEASE CHARACTERISTIC	B
TYPE	• FAZ • Miniature circuit breaker
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	• Switchgear for industrial and advanced commercial applications • xEffect - Switchgear for industrial and advanced commercial applications
NUMBER OF POLES (PROTECTED)	4
NUMBER OF POLES (TOTAL)	4
OPERATIONAL VOLTAGE (IEC/EN 60947-2) - MAX	440 VAC
RATED INSULATION	440 V

VOLTAGE (UI)	
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	5 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICS	7.5 kA
RATED SERVICE SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60947-2) - ICS	7.5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1) - ICN AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC/EN 60898-1)- ICN AT 400 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 230 V	15 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)- ICU AT 400 V	15 kA
RATED SWITCHING CAPACITY (IEC/EN 60898-1)	10 kA
RATED SWITCHING CAPACITY (IEC/EN 60947-2)	15 kA
RATED SWITCHING CAPACITY (IEC/EN 60947-2) AT MAX VOLTAGE RATING	10 kA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
POWER LOSS	6 W

