

Eaton 279145

Eaton Moeller series xEffect - FAZ-DC MCB.
FAZ-DC, 2-pole, tripping characteristic: C,
rated current In: 50 A, Switchgear for DC
applications

PRODUCT NAME	Eaton Moeller series xEffect - FAZ-DC MCB
CATALOG NUMBER	279145
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.245 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947-2 EN45545-2 IEC 61373

USED WITH	Miniature circuit breaker FAZ-DC
AMPERAGE RATING	50 A
FEATURES	Additional equipment possible
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.

CHARACTERISTIC CURVE	eaton-xeffect-faz-dc-mcb-characteristic-curve-002.jpg eaton-xeffect-faz-dc-mcb-characteristic-curve.jpg
DECLARATIONS OF CONFORMITY	DA-DC-03 FAZ-DC eaton-mcb-xeffect-faz-dc-wiring-diagram-002.eps eaton-xeffect-faz-dc-mcb-wiring-diagram-002.jpg
	eaton-xeffect-faz-dc-mcb-catalog-ca003030en-en-us.pdf eaton-xeffect-faz-dc-mcb-dimensions-002.jpg eaton-mcb-xeffect-faz-dimensions-002.eps eaton-mcb-faz-xeffect-faz-3d-drawing-002.eps

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FRAME	45 mm
POLLUTION DEGREE	2
MOUNTING METHOD	Top-hat rail IEC/EN 60715
DEGREE OF PROTECTION	IP20 IP40 (when fitted)
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	9.9 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
ADMISSIBLE BACK-UP FUSE - MAX	100 A gL/gG
BUSBAR MATERIAL THICKNESS	0.8 mm - 2 mm
TERMINAL PROTECTION	Finger and hand touch safe, DGUV VS3, EN 50274
TERMINALS (TOP AND BOTTOM)	Twin-purpose terminals
TRIPPING CHARACTERISTIC	C
AMBIENT OPERATING	75 °C

TEMPERATURE - MAX	
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
ENCLOSURE WIDTH	80 mm
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
DIRECTION OF INCOMING SUPPLY	Polarity dependent
WIDTH IN NUMBER OF MODULAR SPACINGS	2
VOLTAGE RATING AT DC	250 V DC (per pole)
VOLTAGE TYPE	DC
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Two-pole
LIFESPAN, ELECTRICAL	10000 operations
RELEASE CHARACTERISTIC	C
TYPE	• FAZ-DC

	Miniature circuit breaker
SPECIAL FEATURES	Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity
APPLICATION	Switchgear for DC applications
MOUNTING WIDTH	17.5 mm
SELECTIVITY CLASS	3
MOUNTING WIDTH PER POLE	17.5 mm
NUMBER OF POLES (PROTECTED)	2
NUMBER OF POLES (TOTAL)	2
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	50 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	250 V
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 230 V	0 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60898) AT 400 V	0 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 230 V	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2) AT 400 V	10 kA
RATED SWITCHING CAPACITY (IEC/EN 60947- 2)	10 kA
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT	0 W
TERMINAL CAPACITY (CONTROL CABLE)	25 mm ² (1x)
TERMINAL CAPACITY OF SCREW TERMINALS FOR MAIN CABLE	10 mm ² (2x)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

