



□□□□

## Eaton 302448

Eaton xComfort KLV LV systems Final Distribution Boards. Hollow wall compact distribution board, Hybrid, 5-rows, 24MU, super-flat sheet steel door WIFI, 60HWP-W-HY24-SF

□□□□

<b>PRODUCT NAME</b>	Eaton xComfort KLV hybrid distribution board
<b>CATALOG NUMBER</b>	302448
<b>PRODUCT LENGTH/DEPTH</b>	100 mm
<b>PRODUCT HEIGHT</b>	840 mm
<b>PRODUCT WIDTH</b>	360 mm
<b>PRODUCT WEIGHT</b>	6.28 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 60670-24 (PD) IEC/EN 62208



Powering Business Worldwide

<b>SPECIAL FEATURES</b>	IP30 Protection Class II Plastic housing with Wi-Fi door, white (RAL 9016) Note: To obtain protection class II, all devices installed on the mounting plate must be of the fully insulated type.
<b>TYPE</b>	Basic device Installation distribution boards KLV hybrid WIFI
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility.
<b>10.13 MECHANICAL FUNCTION</b>	Meets the product standard's requirements.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	850 °C; meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Not relevant to indoor installations.
<b>10.2.5 LIFTING</b>	Does not apply to enclosures without lifting aids.
<b>10.2.6 MECHANICAL IMPACT</b>	IK05
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	IP30
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Is the panel builder's responsibility.

□□□□	<a href="#">eaton-xcomfort-compact-distribution-boxes-brochure-br014015en-en-us.pdf</a>
□□	<a href="#">eaton-lighting-xcomfort-klv-lv-systems-dimensions-013.eps</a>  <a href="#">eaton-lighting-xcomfort-klv-lv-systems-dimensions-016.eps</a>

<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Protection class 2, therefore not applicable.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Is the panel builder's responsibility.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	U <sub>i</sub> = 400 V AC
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	4 kV
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Meets the product standard's requirements.
<b>FITTED WITH:</b>	<p>Imprintable sheet  Wall trough  Spirit level for leveling  Front cover  Device support rails  Pre-wired power strip with 2x rotating sockets  Microperforated mounting plate  Installation instructions  Hollow-wall anchor  3D adjustment element for mounting designed to adjust the mounting depth by up to 18 mm  Mounting plate  Cable retainer  Neutral and protective conductor terminals with KSK plug-in terminal technology  WIFI Door/Frame  Device holder</p>
<b>ENCLOSURE MATERIAL</b>	Plastic
<b>BUILT-IN HEIGHT</b>	0 mm
<b>BUILT-IN WIDTH</b>	0 mm
<b>CABLE ENTRY POSTION</b>	Cable entries on top and bottom, side, back plate
<b>TERMINAL TYPE</b>	Plug-in terminals
<b>BUILT-IN DEPTH</b>	80 mm
<b>HEAT DISS. AMBIENT 35°C DELTA T:20°C FLUSH MOUNT INDIVID. ENCL. TOP(IEC 60890)</b>	28 W
<b>HEAT DISS. AMBIENT</b>	58 W

<b>35°C DELTA T:35°C FLUSH MOUNT INDIVID. ENCL. TOP(IEC 60890)</b>	
<b>CLOSURE TYPE</b>	Other
<b>COVER/DOOR COLOR</b>	White
<b>COVER/DOOR MODEL</b>	With notch
<b>COVER/DOOR TYPE</b>	Door Single
<b>RAL-NUMBER</b>	9016
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	12
<b>AMBIENT OPERATING TEMPERATURE DETAILS</b>	-5 °C - 40 °C
<b>APPLICATION</b>	Indoor
<b>VOLTAGE RATING AT AC</b>	400 V AC
<b>COLOR</b>	White Traffic white (RAL 9016)
<b>NUMBER OF ROWS</b>	5
<b>FREQUENCY RATING OF CONTACTS</b>	50 Hz
<b>MODULE RACK TYPE</b>	Rail frame / Media mounting plate
<b>DEGREE OF PROTECTION</b>	IK05 IP30
<b>NUMBER OF MODULE SPACE UNITS PER ROW</b>	12
<b>PROTECTION CLASS</b>	II (totally insulated)
<b>PROTECTIVE SHROUDING MATERIAL</b>	Plastic
<b>FUNCTIONS</b>	Basic device Extension possible
<b>MATERIAL</b>	Sheet steel, powder- coated Polystyren (plastic)
<b>MOUNTING METHOD</b>	DIN-rail Hollow-wall mounting Hollow wall
<b>INTERNAL DEPTH</b>	80 mm
<b>PE AND N TERMINAL NUMBER AND CROSS SECTION</b>	N - Fi: 1 x (2.5 mm <sup>2</sup> - 25 mm <sup>2</sup> ) + 7 x (0.5 mm <sup>2</sup> - 4 mm <sup>2</sup> ) N: 2 x (2.5 mm <sup>2</sup> - 25mm <sup>2</sup> ) + 14 x (0.5 mm <sup>2</sup> - 4 mm <sup>2</sup> ) PE: 2 x (2.5 mm <sup>2</sup> - 25 mm <sup>2</sup> ) + 14 x (0.5 mm <sup>2</sup> - 4 mm <sup>2</sup> )

