

Eaton 283214

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breakers 3p 800 A, VE800

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker electronic
CATALOG NUMBER	283214
PRODUCT LENGTH/DEPTH	401 mm
PRODUCT HEIGHT	207 mm
PRODUCT WIDTH	210 mm
PRODUCT WEIGHT	15.52 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC

AMPERAGE RATING	800 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM4
FEATURES	Protection unit Motor drive optional
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to

CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-049.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-048.eps
	eaton-circuit-breaker-nzm-mccb-dimensions-022.eps eaton-circuit-breaker-switch-nzm-mccb-3d-drawing-003.eps

	be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
MOUNTING METHOD	Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	79 W
UTILIZATION CATEGORY	B (IEC/EN 60947-2)
ISOLATION	300 V AC (between the auxiliary contacts) 500 V AC (between auxiliary contacts and main contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE	70 °C

TEMPERATURE - MAX	
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
LIFESPAN, MECHANICAL	10000 operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor terminal Min. 5 segments of 25 mm x 1 mm at rear-side connection (punched) Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal 10 segments of 50 mm x 1 mm (2x) at 1-hole module plate 10 segments of 80 mm x 1 mm (2x) at rear-side width extension Max. 10 segments of 50

	mm x 1 mm (2x) at rear-side connection (punched)
LIFESPAN, ELECTRICAL	<p>2000 operations at 400 V AC-3</p> <p>2000 operations at 690 V AC-1</p> <p>1000 operations at 690 V AC-3</p> <p>2000 operations at 415 V AC-3</p> <p>3000 operations at 415 V AC-1</p> <p>3000 operations at 400 V AC-1</p>
FUNCTIONS	Systems, cable, selectivity and generator protection
TYPE	Circuit breaker
SPECIAL FEATURES	<ul style="list-style-type: none"> • Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity I_{cn}) • R.m.s. value measurement and "thermal memory" • Adjustable time delay setting to overcome current peaks I_r at $6 \times I_r$ also infinity (without overload releases) • Adjustable delay time t_{sd} • Rated current = rated uninterrupted current: 800 A
APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	15 g (half-sinusoidal shock 11 ms)
POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT	Front side

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	800 A
RELEASE SYSTEM	Electronic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 25 ms (≤ 415 V); < 35 ms (> 415 V)
RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)	19.2 kA
RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)	19.2 kA
SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX	8000 A
SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN	800 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	9600 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	1600 A
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 1.5 mm ² (2x) 0.75 mm ² - 2.5 mm ² (1x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 50 mm x 10 mm (2x) direct at switch rear-side connection Min. 25 mm x 5 mm direct at switch rear-side connection Min. 60 mm x 10 mm at rear-side width extension Min. 25 mm x 5 mm at rear-side 1-hole module plate M10 at rear-side screw connection Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate 50 mm x 10 mm (2x) at rear-side 2-hole module plate Max. 80 mm x 10 mm (2x) at rear-side width extension
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	300 mm ² (4x) at rear-side width extension 95 mm ² - 185 mm ² (2x) at rear-side 2-hole module plate 95 mm ² - 300 mm ² (2x) at

	rear-side 1-hole module plate 50 mm ² - 240 mm ² (4x) at 4-hole tunnel terminal 120 mm ² - 300 mm ² (1x) at rear-side 1-hole module plate 35 mm ² - 185 mm ² (4x) at rear-side 2-hole module plate 95 mm ² - 240 mm ² (6x) at rear-side width extension
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	50 mm ² (4x) at rear-side 2- hole module plate 240 mm ² (2x) at rear-side width extension 70 mm ² - 185 mm ² (2x) at rear-side 1-hole module plate 70 mm ² - 240 mm ² (6x) at rear-side width extension 185 mm ² - 240 mm ² (1x) at rear-side 1-hole module plate
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	50 mm ² - 185 mm ² (4x) direct at switch rear-side connection 120 mm ² - 185 mm ² (1x) direct at switch rear-side connection
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	50 mm ² - 240 mm ² (4x) at 4-hole tunnel terminal
HANDLE TYPE	Rocker lever
SHORT DELAY CURRENT SETTING (ISD) - MAX	8000 A
SHORT DELAY CURRENT SETTING (ISD) - MIN	800 A
INSTANTANEOUS CURRENT SETTING (II) - MAX	9600 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	1600 A
NUMBER OF OPERATIONS PER HOUR - MAX	60
OVERLOAD CURRENT SETTING (IR) - MAX	800 A
OVERLOAD CURRENT SETTING (IR) - MIN	400 A
RATED SHORT-CIRCUIT	63 kA

BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	43 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	49 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	37 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	220 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	187 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	143 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	105 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Connection on rear. Strip terminal. Tunnel terminal
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	275 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V
RATED INSULATION VOLTAGE (UI)	1000 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

