

Eaton 32D33

Fuse-link, LV, 32 A, AC 500 V, D3, gL/gG, IEC, time-delay

| | |
|-------------------------|--|
| | |
| PRODUCT NAME | Eaton Bussmann series low voltage D fuse |
| CATALOG NUMBER | 32D33 |
| PRODUCT LENGTH/DEPTH | 50 mm |
| PRODUCT HEIGHT | 27 mm |
| PRODUCT WIDTH | 27 mm |
| PRODUCT WEIGHT | 51 g |
| COMPLIANCES | CE Marked RoHS Compliant |
| CERTIFICATIONS | IEC 60269 EAC DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301 |

| | |
|---|--|
| | |
| AMPERAGE RATING | 32 A |
| FUSE SIZE | DIII |
| BREAKING CAPACITY | 50 kA |
| CONSTRUCTION SIZE (FUSE INSERTS) | DIII |
| RATED VOLTAGE AC | 500 V |
| CLASS | Class C gL/gG |
| FUSE TYPE | D33 - Time delay |
| ACCESSORY/SPARE PART TYPE | 35GD33 Black screw cap gauge piece |
| UTILIZATION CATEGORY | gG (cable protection/equipment protection) |
| COLOR | Black |
| INTERRUPT RATING | 50 kAIC |
| FUSE INDICATOR | Non-indicating |
| CONNECTION | Other |
| CONSTRUCTION | D3 |
| CONSTRUCTION SIZE | DIII |
| FUSE SHAPE | Bottle |
| RESPONSE TIME | Time-delay |
| SUITABLE FOR | E33/DIII Fuse base TFD33 Fuse base screw fixing SFRD33 Fuse base DIN-Rail mount TFRD33 Fuse base DIN-Rail mount |
| MATERIAL | White ceramic body |
| RELEASE CHARACTERISTIC | Time-lag |
| VOLTAGE RATING | 500 V |
| TYPE | Fuse |
| APPLICATION | For domestic and general industrial applications |

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-d-fuse-declaration-of-conformity-uk251016en.pdf](#)

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

