

Eaton 32LET

Eaton Bussmann series high speed British standard fuse, 32A, 280 VAC/150 VDC (UL), Class aR, 200 kA RMS Sym.

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	32LET
UPC	051712833929
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	31.4 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized Designed and tested to BS88 part 4 IEC 60269-4

AMPERAGE RATING	32 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	280 V
RATED VOLTAGE DC	150 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	41 mm
MOUNTING DIMENSION	M6
CURRENT TYPE	AC
CLASS	Class aR
CLEARING (I2T)	450
WATT LOSSES	5 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I2T)	32
COLOR	None
INTERRUPT RATING	200 kAIC 200 kA RMS Sym, 50 kA DC at 150 Vdc
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	280 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	LET
SUITABLE FOR	TI500 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY	DA-DC-00004685
	DA-DC-00004682

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

