



□□□□□

Eaton 35D33

Eaton Bussmann series low voltage D fuse, 500V, 35A, 50 kAIC, Non Indicating, fuse, Class C gL/gG, Time delay, Black, Ceramic body

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	35D33
UPC	051712834148
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	27 mm
PRODUCT WIDTH	27 mm
PRODUCT WEIGHT	51 g
COMPLIANCES	CE Marked GoST-R RoHS Compliant
CERTIFICATIONS	VDE IEC 60269 DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301



Powering Business Worldwide

□□□□

AMPERAGE RATING	35 A
FUSE SIZE	DIII
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DIII
RATED VOLTAGE AC	500 V
CLASS	Class C gL/gG
FUSE TYPE	D33 - Time delay
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
ACCESSORY/SPARE PART TYPE	35GD33 Black screw cap gauge piece
COLOR	Black
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D3
CONSTRUCTION SIZE	DIII
FUSE SHAPE	Bottle
RESPONSE TIME	Time-delay
SUITABLE FOR	E33/DIII Fuse base TFD33 Fuse base screw fixing SFRD33 Fuse base DIN-Rail mount TFRD33 Fuse base DIN-Rail mount
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Time-lag
QUANTITY	25
VOLTAGE RATING	500 V
TYPE	fuse
APPLICATION	For domestic and general industrial applications

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-d-fuse-declaration-of-conformity-uk251016en.pdf](#)

