



## Eaton 35NHFF1BI-400

Eaton Bussmann series Fuse-link, LV, 35 A, AC 400 V, NH1, gFF, IEC, dual indicator, insulated gripping lugs

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage NH Fuse
<b>CATALOG NUMBER</b>	35NHFF1BI-400
<b>PRODUCT LENGTH/DEPTH</b>	135 mm
<b>PRODUCT HEIGHT</b>	63 mm
<b>PRODUCT WIDTH</b>	40 mm
<b>PRODUCT WEIGHT</b>	348 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269-1 IEC 60269-2 DIN 43620

□□□□

AMPERAGE RATING	35 A
FITTED WITH:	Insulated metal gripping lugs
FUSE SIZE	NH1
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	400 V
CLASS	Class gFF
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gFF(full-range, extra fast operation)
COLOR	None
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	Yes
WATT LOSSES	5.5 W
CONNECTION	Blade end
CONSTRUCTION	NH1
CONSTRUCTION SIZE	NH1
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD1-D Single pole NH Fuse base Microswitch 170H0236 TD1-D Triple pole NH Fuse base
MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	industrial
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system A
RATED SWITCHING CAPACITY AC	120 kA

□□

DECLARATIONS OF  
CONFORMITY[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250985en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



Eaton House  
30 Pembroke Road  
Dublin 4,     
Eaton.com

© 2025   

Follow us on social media to get the latest product and support information.

