



□□□□□

Eaton 40071352008

Eaton monitoring interfaces CG-S module V-CG-SB.1 DALI monitoring module (without packing)

□□□□

PRODUCT NAME	Eaton monitoring interfaces CG-S module
CATALOG NUMBER	40071352008
PRODUCT LENGTH/DEPTH	145 mm
PRODUCT HEIGHT	21 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.047 kg
CERTIFICATIONS	CE

□□□□

□□

LAMP TYPE	Other
NOMINAL VOLTAGE - MAX	240 V
NOMINAL VOLTAGE - MIN	220 V
PROTECTION CLASS	I
NOMINAL VOLTAGE RANGE DC - MAX	275 V
NOMINAL VOLTAGE RANGE DC - MIN	176 V
ADDITIONAL DATA LINE NEEDED	Yes
AMBIENT TEMPERATURE - MAX	60 °C
AMBIENT TEMPERATURE - MIN	-20 °C
CONNECTION TERMINALS (IN)	2.5 mm ²
CONNECTION TERMINALS (OUT)	1.5 mm ²
ENEC CERTIFIED	Yes
HOUSING COLOR	Grey
HOUSING MATERIAL	Flame retardant polycarbonate
MAXIMAL NUMBER OF MONITORED LUMINAIRES PER CIRCUIT	20
REVERSE-POLARITY PROTECTED TERMINALS (IN)	Yes
SLI-TECHNOLOGY	No
ADJUSTABLE LUMINOUS FLUX IN DC MODE	10 % - 100 % (in 10 % steps)
PRODUCT BRANDING	Eaton
DEGREE OF PROTECTION (IP)	IP20
MAXIMAL PERMISSIBLE TEST POINT TEMPERATURE	65 °C
LINE LENGTH - MAX	1 m
OPERATING FREQUENCY	60 Hz
STANDBY POWERLOSS AT 230 V / 50 HZ	1 W
PROTECTION CLASS ACCORDING TO IEC 61140	None

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

