



Eaton 288852

Eaton Moeller® series M22 Threaded ring,
wall thickness 7mm

□□□□

PRODUCT NAME	Eaton Moeller® series M22 Accessory Threaded ring
CATALOG NUMBER	288852
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.002 kg
CERTIFICATIONS	CSA-C22.2 No. 94-91 CSA File No.: 012528 UL Category Control No.: NKCR UL File No.: E29184 CSA Class No.: 3211-03 CSA-C22.2 No. 14-05 UL 508 IEC/EN 60947-5 UL CE CSA

**ACCESSORY/SPARE PART
TYPE**

Spare part

10.10 TEMPERATURE RISE

Not applicable.

**10.11 SHORT-CIRCUIT
RATING**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.12 ELECTROMAGNETIC
COMPATIBILITY**

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.13 MECHANICAL
FUNCTION**

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION
RESISTANCE**

Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF
THERMAL STABILITY OF
ENCLOSURES**

Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF
RESISTANCE OF
INSULATING MATERIALS
TO NORMAL HEAT**

Meets the product standard's requirements.

**10.2.3.3 RESIST. OF
INSUL. MAT. TO
ABNORMAL HEAT/FIRE
BY INTERNAL ELECT.
EFFECTS**

Meets the product standard's requirements.

**10.2.4 RESISTANCE TO
ULTRA-VIOLET (UV)
RADIATION**

Please enquire

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

**10.2.6 MECHANICAL
IMPACT**

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

**10.3 DEGREE OF
PROTECTION OF
ASSEMBLIES**

Does not apply, since the entire switchgear needs to be evaluated.

**10.4 CLEARANCES AND
CREEPAGE DISTANCES**

Meets the product standard's requirements.

**10.5 PROTECTION
AGAINST ELECTRIC
SHOCK**

Does not apply, since the entire switchgear needs to be evaluated.

□□□□□

[IL04716002Z](#)

□□/□□

[RMQ small E-Stop
emergency-stop button](#)

10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
CONNECTION TO SMARTWIRE-DT	No
ELECTRICAL ACCESSORY TYPE	Other
MECHANICAL ACCESSORY TYPE	Other
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

