



## Eaton 40071356738

Eaton GuideLed SL 13032.2 CG-S square surface mounting luminaire with asymmetric narrow beam optics for mounting heights up to 17m or for higher illuminance levels, e.g. 10.8 lx, 4000 K including LED-Supply and CG-S technology 20 addresses



<b>PRODUCT NAME</b>	Eaton GuideLed SL CG-S Emergency luminaire
<b>CATALOG NUMBER</b>	40071356738
<b>PRODUCT LENGTH/DEPTH</b>	124 mm
<b>PRODUCT HEIGHT</b>	32 mm
<b>PRODUCT WIDTH</b>	124 mm
<b>PRODUCT WEIGHT</b>	0.33 kg
<b>CERTIFICATIONS</b>	CE



Powering Business Worldwide



<b>BATTERY QUALITY</b>	Not applicable
<b>PROTECTION CLASS</b>	I
<b>OUTDOOR USE COMPLIANCE</b>	False
<b>EXPLOSION PROTECTED</b>	False
<b>DEGREE OF PROTECTION</b>	IP41
<b>LAMP TYPE</b>	LED not exchangeable
<b>WITH LIGHT SOURCE</b>	True
<b>LAMP HOLDER</b>	None
<b>LAMP POWER</b>	2.2 W
<b>TYPE OF INDICATOR</b>	Not applicable
<b>MONITORING EQUIPMENT</b>	Safety module for monitoring (central feeded system)
<b>POWER SUPPLY SYSTEM</b>	Central (central battery)
<b>VOLTAGE TYPE</b>	AC/DC
<b>CURRENT CONSUMPTION AT 220V DC</b>	20 mA
<b>APPARENT POWER AT MAINS OPERATION</b>	8 VA
<b>POWER FACTOR</b>	0.59
<b>WIRING SYSTEM</b>	Continuous circuit/emergency circuit
<b>WITH REMOTE SWITCH CONNECTION</b>	True
<b>RESERVE-POLARITY PROTECTED</b>	True
<b>ENERGY EFFICIENCY CLASS</b>	A
<b>CONDUCTOR CROSS SECTION</b>	2.5
<b>CONNECTION TYPE</b>	Plug-in connection
<b>LED NOMINAL CURRENT AT CONSTANT CURRENT</b>	20 mA
<b>MAX. SYSTEM POWER</b>	3.9 W
<b>RATED LIFE TIME L80/B10 AT 25 °C</b>	100000 hour
<b>TYPE OF CONTROL GEAR</b>	LED operating device current-controlled
<b>TYPE OF WIRING</b>	Suitable for through wiring
<b>NOMINAL VOLTAGE AC - MAX</b>	240 V
<b>NOMINAL VOLTAGE AC - MIN</b>	220 V
<b>NOMINAL VOLTAGE DC</b>	275 V



<b>RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN</b>	-20 °C
<b>RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX</b>	40 °C
<b>INRUSH CURRENT</b>	1.5
<b>SUITABLE FOR STANDBY SWITCHING</b>	No
<b>SUITABLE FOR CONTINUOUS CIRCUIT</b>	No
<b>RAL-NUMBER (SIMILAR) HOUSING</b>	9016
<b>MOUNTING METHOD</b>	Ceiling surface mounting
<b>MATERIAL HOUSING</b>	Plastic
<b>COLOR HOUSING</b>	White
<b>MATERIAL COVER</b>	Without cover
<b>PICTOGRAM INCLUDED</b>	False
<b>NUMBER OF POLES (NUMERIC)</b>	3
<b>IMPACT STRENGTH</b>	IK03
<b>RATED LUMINOUS FLUX ACC. IEC 62722-2-1</b>	320 lm
<b>COLOR TEMPERATURE - MAX</b>	4000 K
<b>COLOR TEMPERATURE - MIN</b>	4000 K
<b>LIGHT DISTRIBUTOR</b>	Focal lens
<b>ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP</b>	A++, A+, A (LED)
<b>ENERGY EFFICIENCY CLASS OF THE PROVIDED EXCHANGEABLE BUILT-IN LAMP</b>	A++
<b>FUNCTION</b>	Escape route lighting
<b>COLOR OF LIGHT</b>	White
<b>COLOR RENDERING INDEX (CRI)</b>	70
<b>LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D</b>	False
<b>LUMINOUS FLUX IN STANDBY MODE</b>	320 lm
<b>FREQUENCY</b>	50/60 Hz
<b>MAIN CONNECTION TERMINAL</b>	2.5mm <sup>2</sup>
<b>PRODUCT BRANDING</b>	Eaton
<b>SHAPE</b>	Square
<b>APPLICATION</b>	ENEC certified

