

Eaton 289146

Eaton Moeller® series DILM Replacement coil, RA 110: 48 - 110 V 40-60 Hz/48 - 110 V DC, AC and DC operation, For use with: DILM580, DILM650, DILM750, DILM820, DILM1000

PRODUCT NAME	Eaton Moeller® series DILM replacement coil
CATALOG NUMBER	289146
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	175 mm
PRODUCT WIDTH	135 mm
PRODUCT WEIGHT	1.31 kg
CERTIFICATIONS	IEC/EN 60947-4-1 UL Category Control No.: NLDX UL CSA-C22.2 No. 14-05 UL 508 UL File No.: E29096 CSA Class No.: 3211-04 CSA File No.: 012528 CE CSA

ACCESSORIES

Individual coils

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF PROTECTION OF ASSEMBLIES

Does not apply, since the entire switchgear needs to be evaluated.

10.4 CLEARANCES AND CREEPAGE DISTANCES

Meets the product standard's requirements.

10.5 PROTECTION AGAINST ELECTRIC SHOCK

Does not apply, since the entire switchgear needs to be evaluated.

10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS

Does not apply, since the entire switchgear needs to be evaluated.

10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
VOLTAGE TYPE	AC/DC
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	48 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	48 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	48 V
PRODUCT CATEGORY	Accessories

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

