

Eaton 400LMT

Eaton Bussmann series high speed British standard fuse, Single barrel, 400A, 240 VAC/150 VDC (IEC), 250 VAC/150 VDC (UL), Class aR, Breaking capacity 200 kA RMS Sym., 40 kA DC at 150 VDC (IEC). 50 kA at 150 VDC (UL)

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	400LMT
UPC	051712834933
PRODUCT LENGTH/DEPTH	52 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	126 mm
PRODUCT WEIGHT	185 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated Designed and tested to BS88 part 4 UL recognized IEC 60269-4 CCC

AMPERAGE RATING	400 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	240 V
RATED VOLTAGE DC	150 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	58.1 mm
MOUNTING DIMENSION	M10
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I2T)	160000
WATT LOSSES	40 W
FUSE SHAPE	Offset bolted tags
PRE ARC (I2T)	1400
COLOR	None
INTERRUPT RATING	200 kA RMS Sym, 40 kA at 150 Vdc (IEC) 200 kA RMS Sym, 50 kA at 150 Vdc (UL)
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Stud
PACKAGING TYPE	Standard
VOLTAGE RATING	240 Vac, 150 Vdc
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	LMT
SUITABLE FOR	MC-250 Trip indicator kit (indicator + clips) TI250 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor

DECLARATIONS OF CONFORMITY	DA-DC-00004685
	DA-DC-00004682

FUSE SYSTEM
(ACCORDING TO IEC
60269)

Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

