



Eaton 292461

Eaton xEnergy Basic LV systems Low voltage switchgear. White door with inspection window, 800/7-W

□□□□

PRODUCT NAME	Eaton xEnergy Basic door
CATALOG NUMBER	292461
PRODUCT LENGTH/DEPTH	45 mm
PRODUCT HEIGHT	710 mm
PRODUCT WIDTH	815 mm
PRODUCT WEIGHT	2.65 kg
COMPLIANCES	RoHS conform

□□□□		□□	
TYPE	Additional equipment		
FEATURES	Version as glazed door		
SURFACE FINISHING	With powder coating Powder coating		
COLOR	White Traffic white (RAL 9016)		
DEGREE OF PROTECTION	IP30 NEMA Other		
SUITABLE FOR HEIGHT	760 mm		
SUITABLE FOR WIDTH	800 mm		
COVER/DOOR COLOR	Transparent		
COVER/DOOR TYPE	Three-point turn-lock		
MATERIAL	Sheet steel/plastic Steel		
HOUSING MATERIAL	Sheet steel/plastic		
MODEL	Stop door		
MOUNTING METHOD	Surface mounting		
FUNCTIONS	Additional equipment		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:

