



## Eaton 293559

Eaton xEnergy Basic LV systems Low voltage switchgear. Cable entry / flange plate for W=1000mm, closed, white

□□□□

|                             |                                     |
|-----------------------------|-------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton xEnergy Basic other accessory |
| <b>CATALOG NUMBER</b>       | 293559                              |
| <b>PRODUCT LENGTH/DEPTH</b> | 175 mm                              |
| <b>PRODUCT HEIGHT</b>       | 20 mm                               |
| <b>PRODUCT WIDTH</b>        | 945 mm                              |
| <b>PRODUCT WEIGHT</b>       | 1.3 kg                              |
| <b>COMPLIANCES</b>          | RoHS conform                        |

| □□□□                                   |                          |
|----------------------------------------|--------------------------|
| TYPE                                   | Additional equipment     |
| NUMBER OF CONNECTOR HOLES              | 0                        |
| SUITABLE FOR NOMINAL THREAD (PG) - MAX | 50                       |
| SUITABLE FOR NOMINAL THREAD (PG) - MIN | 10                       |
| SUITABLE FOR WIDTH                     | 1000 mm                  |
| SURFACE FINISHING                      | With powder coating      |
| CABLE ENTRY TYPE                       | Blind                    |
| COLOR                                  | Traffic white (RAL 9016) |
| DEGREE OF PROTECTION                   | IP30<br>Other            |
| SURFACE PROTECTION                     | Powder coating           |
| SHAPE                                  | Straight                 |
| MATERIAL                               | Steel<br>Sheet steel     |
| HOUSING MATERIAL                       | Sheet steel              |
| MODEL                                  | Blind                    |
| MOUNTING METHOD                        | Surface mounting         |
| FUNCTIONS                              | Additional equipment     |
| THREAD TYPE                            | None                     |
| THICKNESS                              | 1 mm                     |
| SUITABLE FOR CABLE DIAMETER - MAX      | 0 mm                     |
| SUITABLE FOR CABLE DIAMETER - MIN      | 0 mm                     |

□□

|       |
|-------|
| □□□□: |
| □□□□: |
| □□□:  |
| □□:   |