



Eaton 531034FULL-0090

Eaton, Alarms & signalling devices, Fulleon, Solex Xenon beacon, Blue lens, Deep white base, 10Cd (SO/B/DW/10C)

□□□□

PRODUCT NAME	Eaton Solex Xenon fire alarm beacon
CATALOG NUMBER	531034FULL-0090
PRODUCT LENGTH/DEPTH	93 mm
PRODUCT HEIGHT	93 mm
PRODUCT WIDTH	93 mm
PRODUCT WEIGHT	0.18 kg
COMPLIANCES	CE marking
CERTIFICATIONS	CE



Powering Business Worldwide

□□□□

□□

NOMINAL VOLTAGE	24 V
VOLTAGE TYPE	DC
ELECTRICITY CONSUMPTION	0.088 A
POWER	2.1 W
LENS COLOR	Blue
MATERIAL HOUSING	Plastic
COLOR HOUSING	White
MOUNTING METHOD	Surface mounting
NUMBER OF MODES	1
STANDBY-TIME UP TO	0 hour
AMBIENT TEMPERATURE - MAX	70 °C
AMBIENT TEMPERATURE - MIN	-25 °C
LAMP TYPE	Incandescent lamp
LAMP HOLDER	Other
DEGREE OF PROTECTION (IP)	IP65
ADDRESSING MODE	Hard addressing
ALARM CURRENT - MAX	185 mA
ALARM CURRENT - MIN	45 mA
CONSTRUCTION MATERIAL	PC
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
OPERATING TEMPERATURE - MAX	70 °C
OPERATING TEMPERATURE - MIN	-25 °C
STANDBY CURRENT	0
SYSTEM TYPOLOGY	Conventional (Non-addressable)
PRODUCT BRANDING	Eaton
NOMINAL VOLTAGE - MIN	12 V
NOMINAL VOLTAGE - MAX	48 V
ELECTRICITY CONSUMPTION - MIN	0.045 A
ELECTRICITY CONSUMPTION - MAX	0.185 A
INTEGRATED FUNCTION	Flashlight

CABLE ENTRY	M20 hole
MOUNTING POSITION	Wall surface (internal) Wall (weatherproof)
LIGHT COLOR	Blue
SYSTEM WIRING	0.28 - 2.5 mm
DIMMABLE	No
FUNCTION ROTATING LIGHT	NO
WITH INFRARED	NO

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

