

Eaton 5P1150I-TH

Eaton 5P UPS, 1150 VA, 600 W, Input: C14,
Outputs: (8) C13, Tower

PRODUCT NAME	Eaton 5P UPS
CATALOG NUMBER	5P1150I-TH
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	230 mm
PRODUCT WIDTH	345 mm
PRODUCT WEIGHT	11.12 kg
COMPLIANCES	TUV TISI CB
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 EN 62040-3

TOPOLOGY	Line-interactive
FORM FACTOR	Tower
CONSTRUCTION TYPE	Free standing model
COLOR	Black/silver
RACK MOUNTING KIT	No
AUTO SHUTDOWN FUNCTION	Yes
INPUT CONNECTION	C14
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50-60 Hz
INPUT FREQUENCY RANGE	47–70 Hz (50 Hz system), 56.5–70 Hz (60 Hz system), 40 Hz in low-sensitivity mode
RECEPTACLE	(8) C13
OUTPUT WAVEFORM	Sine wave
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
RUNTIME GRAPH	View runtime graph
BATTERY MANAGEMENT	ABM or constant voltage charging method (user selectable), automatic battery test, deep discharge protection
BATTERY REPLACEMENT	User replaceable
BATTERY RATING	12V/9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	None; See Eaton 5PX UPS for extended runtimes options
EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	2000 m



BTU RATING	Online: 158
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-90% non-condensing
TEMPERATURE RANGE	0° to 35°C (32° to 95°F)
BATTERY QUANTITY	2
EFFICIENCY AT MAX. LOAD	97%
INPUT VOLTAGE RANGE	160-294 V (adjustable to 150 V-294 V)
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.7
OUTPUT VOLTAGE RANGE	230 V (+6%/-10%)
PHASE (INPUT)	Single-phase
PHASE (OUTPUT)	Single-phase
RUNTIME AT FULL LOAD	4 min

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

