

Eaton 3-4918-112A

Eaton DG1 Variable frequency drive, 400 V AC, 3-phase, 1040 A, 560 kW, IP00, Brake chopper, DC link choke

PRODUCT NAME	Eaton DG1 variable frequency drive
CATALOG NUMBER	3-4918-112A
PRODUCT LENGTH/DEPTH	561 mm
PRODUCT HEIGHT	1538 mm
PRODUCT WIDTH	1037 mm
PRODUCT WEIGHT	820 kg
CERTIFICATIONS	C-Tick IEC/EN 61800-3 RoHS, ISO 9001 CE Safety requirements: IEC/EN 61800-5 UL File No.: E134360 UL Category Control No.: NMMS, NMMS7 Specification for general requirements: IEC/EN 61800-2 CUL UL UkrSEPRO EAC

FEATURES	Externally accessible fan Temperature-controlled fan
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
FITTED WITH:	Additional PCB protection IGBT inverter Brake chopper Internal DC link Multi-line graphic display Radio interference suppression filter DC link choke Breaking resistance Control unit PC connection

MCAD MODEL	dg1_18.dwg dg1_18.stp
	eaton-profinet-de1-dc1-da1-dg1-dm1-dx1-mn040062-en-en.pdf

POLLUTION DEGREE	2
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	Yes In conjunction with DXG-NET-SWD SmartWire DT module
OPERATING MODE	U/f control Torque regulation Sensorless vector control (SLV) Speed control with slip compensation
FRAME SIZE	FS8
AIR VOLUME CAPACITY	2800 m³/h
ALTITUDE	Above 1000 m with 1 % derating per 100 m Max. 2000 m for Corner Grounded TN Systems Max. 1000 m Max. 3000 m
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	40 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 400 V	817.5 kVA

APPARENT POWER AT 480 V	1021.9 kVA
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 110% OVERLOAD	1099 A
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	977 A
MOUNTING POSITION	Vertical
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	65 kA
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RESOLUTION	0.01 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	215 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	850 VDC
VOLTAGE RATING - MAX	500 VAC
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	SmartWire-DT, optional Modbus RTU, built in BACnet MS/TP, built in Modbus TCP, built in CANopen®, optional Ethernet IP, built in DeviceNet, optional PROFIBUS, optional
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP00 NEMA Other
PROTOCOL	BACnet CAN DeviceNet EtherNet/IP MODBUS

	Other bus systems PROFIBUS PROFINET IO TCP/IP
ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	1035 A
ASSIGNED MOTOR CURRENT IM AT 440/480 V, 60 HZ, 110% OVERLOAD	1160 A
ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 110% OVERLOAD	1116.8 A
ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 150% OVERLOAD	1025 A
SYSTEM CONFIGURATION TYPE	TN-S, TN-C, TN-C-S, TT, IT
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ	900 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 110% OVERLOAD	1000 HP
BRAKING RESISTANCE	1.4 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	18776 W
INPUT CURRENT ILN AT 110% OVERLOAD	1164 A
INPUT CURRENT ILN AT 150% OVERLOAD	1030 A
MAINS CURRENT DISTORTION	28 %
CURRENT LIMITATION	0.1 - 2 x I _H (CT), motor, main circuit
NUMBER OF SLOTS	2 (expansion)
BRAKING TORQUE	Adjustable to 150 %, DC - Main circuit Max. 30 % MN, Standard - Main circuit Max. 100 % of rated operational current I _e with external braking resistor - Main circuit Adjustable to 150 % (I/I _e),

	DC - Main circuit
CABLE LENGTH	<p>C3 ≤ 50 m, Radio interference level, maximum motor cable length</p> <p>C2 ≤ 10 m, Radio interference level, maximum motor cable length</p> <p>200 m, screened, maximum permissible, Motor feeder</p>
FUNCTIONS	4-quadrant operation possible
OUTPUT VOLTAGE (U2)	<p>500 V AC, 3-phase</p> <p>400 V AC, 3-phase</p> <p>480 V AC, 3-phase</p>
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	8
RADIO INTERFERENCE CLASS	<p>Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments</p> <p>C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.</p> <p>C1: with external filter, for conducted emissions only</p>
NUMBER OF OUTPUTS (DIGITAL)	1
STARTING CURRENT - MAX	<p>200 %, I_H, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section</p>
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	<p>3 (parameterizable, 2 changeover contacts and 1 N/O, 6 A (240 V AC) / 6 A (24 V DC))</p>
NUMBER OF PHASES (OUTPUT)	3
RATED CONTROL SUPPLY	10 V DC (U _s , max. 10 mA)

VOLTAGE	
EFFICIENCY	97.4 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 250 mA options incl.)
SUPPLY FREQUENCY	50/60 Hz
MAINS VOLTAGE - MAX	500 V
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I_{2N}	920 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	1
NUMBER OF HW-INTERFACES (OTHER)	1
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	500 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	630 kW
OUTPUT FREQUENCY - MAX	400 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	500 V
OVERLOAD CURRENT I_L AT 110% OVERLOAD	1298 A
OVERLOAD CURRENT I_L AT 150% OVERLOAD	1560 A
SHOCK RESISTANCE	UPS drop test (for weights inside the UPS frame)

	Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 Storage and transportation: maximum 15 g, 11 ms (inside the packaging)
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	2 kHz, 1.5 - 6 kHz adjustable, fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	400 V AC, 3-phase 500 V AC, 3-phase 480 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	2 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
VIBRATION	Resistance: 15.8 – 150 Hz, 1 g, Maximum acceleration amplitude Resistance: 5 - 15.8 Hz, Amplitude 1 mm (peak) Resistance: 5 - 150 Hz, According to EN 61800-5- 1, IEC/EN 60068-2-6
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD	1180 A
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	1040 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	1040 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ	560 kW
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 110% OVERLOAD	630 kW
RATED OPERATIONAL POWER AT 500 V, 50 HZ	750 kW
RATED OPERATIONAL POWER AT 500 V, 50 HZ, 110% OVERLOAD	800 kW
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL1, PLc Cat 1)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

