



□□□□□

Eaton 3-4918-305A

Eaton DG1 Variable frequency drive, 600 V AC, 3-phase, 520 A, 355 kW, IP00, DC link choke

□□□□

PRODUCT NAME	Eaton DG1 variable frequency drive
CATALOG NUMBER	3-4918-305A
PRODUCT LENGTH/DEPTH	561 mm
PRODUCT HEIGHT	980 mm
PRODUCT WIDTH	1037 mm
PRODUCT WEIGHT	410 kg
CERTIFICATIONS	CUL C-Tick Specification for general requirements: IEC/EN 61800-2 UkrSEPRO UL RoHS, ISO 9001 IEC/EN 61800-3 CE Safety requirements: IEC/EN 61800-5 EAC



Powering Business Worldwide

FEATURES	Temperature-controlled fan Externally accessible fan
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
FITTED WITH:	Additional PCB protection Multi-line graphic display DC link choke IGBT inverter Radio interference suppression filter Internal DC link Control unit PC connection
POLLUTION DEGREE	2

MCAD MODEL	dg1_18_2.dwg dg1_18_2.stp
□□□□	eaton-profinet-de1-dc1-da1-dg1-dm1-dx1-mn040062-en-en.pdf

CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	In conjunction with DXG-NET-SWD SmartWire DT module Yes
OPERATING MODE	U/f control Sensorless vector control (SLV) Speed control with slip compensation Torque regulation
FRAME SIZE	FS8
AIR VOLUME CAPACITY	2800 m³/h
ALTITUDE	Above 1000 m with 1 % derating per 100 m Max. 2000 m Max. 1000 m
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	40 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 600 V	613.1 kVA
APPARENT POWER AT 690 V	705.1 kVA
MOUNTING POSITION	Vertical
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	65 kA

RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RATED OPERATIONAL POWER AT 525 V, 50 HZ	355 kW
RATED OPERATIONAL POWER AT 525 V, 50 HZ, 110% OVERLOAD	400 kW
RATED OPERATIONAL POWER AT 600 V, 50 HZ	400 kW
RATED OPERATIONAL POWER AT 600 V, 50 HZ, 110% OVERLOAD	450 kW
RESOLUTION	0.01 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	291 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	1050 VDC
VOLTAGE RATING - MAX	690 VAC
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	Modbus RTU, built in SmartWire-DT, optional BACnet MS/TP, built in DeviceNet, optional Modbus TCP, built in Ethernet IP, built in CANopen®, optional PROFIBUS, optional
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP00 NEMA Other
PROTOCOL	BACnet CAN DeviceNet EtherNet/IP MODBUS Other bus systems PROFIBUS PROFINET IO TCP/IP
ASSIGNED MOTOR	547 A

CURRENT IM AT 525 V, 50 HZ, 110% OVERLOAD	
ASSIGNED MOTOR CURRENT IM AT 525 V, 50 HZ, 150% OVERLOAD	495.2 A
ASSIGNED MOTOR CURRENT IM AT 600 V, 50 HZ, 110% OVERLOAD	535 A
ASSIGNED MOTOR CURRENT IM AT 600 V, 50 HZ, 150% OVERLOAD	486 A
ASSIGNED MOTOR CURRENT IM AT 690 V, 60 HZ, 110% OVERLOAD	550 A
ASSIGNED MOTOR CURRENT IM AT 690 V, 60 HZ, 150% OVERLOAD	500 A
SYSTEM CONFIGURATION TYPE	TN-S, TN-C, TN-C-S, TT, IT
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 690 V, 60 HZ	650 HP
ASSIGNED MOTOR POWER AT 690 V, 60 HZ, 110% OVERLOAD	700 HP
BRAKING RESISTANCE	2.5 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	11486 W
INPUT CURRENT ILN AT 110% OVERLOAD	597 A
INPUT CURRENT ILN AT 150% OVERLOAD	527 A
MAINS CURRENT DISTORTION	28 %
CURRENT LIMITATION	0.1 - 2 x I _H (CT), motor, main circuit
NUMBER OF SLOTS	2 (expansion)
BRAKING TORQUE	Max. 30 % MN, Standard - Main circuit Max. 100 % of rated operational current I _e with external braking resistor - Main circuit Adjustable to 150 %, DC - Main circuit Adjustable to 150 % (I/I _e), DC - Main circuit
CABLE LENGTH	C3 ≤ 10 m, Radio interference level, maximum motor cable

	length 200 m, screened, maximum permissible, Motor feeder
OUTPUT VOLTAGE (U2)	600 V AC, 3-phase 690 V AC, 3-phase
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	8
RADIO INTERFERENCE CLASS	C1: with external filter, for conducted emissions only C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
NUMBER OF OUTPUTS (DIGITAL)	1
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	3 (parameterizable, 2 changeover contacts and 1 N/O, 6 A (240 V AC) / 6 A (24 V DC))
NUMBER OF PHASES (OUTPUT)	3
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 10 mA)
EFFICIENCY	98.1 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 250 mA options incl.)
SUPPLY FREQUENCY	50/60 Hz
MAINS VOLTAGE - MAX	600 V
MAINS VOLTAGE - MIN	525 V
NOMINAL OUTPUT CURRENT I2N	520 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	1

NUMBER OF HW-INTERFACES (OTHER)	1
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	373 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	448 kW
OUTPUT FREQUENCY - MAX	400 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	600 V
OVERLOAD CURRENT IL AT 110% OVERLOAD	649 A
OVERLOAD CURRENT IL AT 150% OVERLOAD	780 A
SHOCK RESISTANCE	Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 UPS drop test (for weights inside the UPS frame) Storage and transportation: maximum 15 g, 11 ms (inside the packaging)
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	2 kHz, 1.5 - 6 kHz adjustable, fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	600 V AC, 3-phase 690 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	2 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker),

	Power Wiring
VIBRATION	Resistance: 5 - 150 Hz, According to EN 61800-5- 1, IEC/EN 60068-2-6 Resistance: 15.8 – 150 Hz, 1 g, Maximum acceleration amplitude Resistance: 5 - 15.8 Hz, Amplitude 1 mm (peak)
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD	590 A
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	520 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	520 A
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL1, PLc Cat 1)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

