

# Eaton 3-4918-306A

Eaton DG1 Variable frequency drive, 600 V  
AC, 3-phase, 520 A, 355 kW, IP00, Brake  
chopper, DC link choke

PRODUCT NAME	Eaton DG1 variable frequency drive
CATALOG NUMBER	3-4918-306A
PRODUCT LENGTH/DEPTH	561 mm
PRODUCT HEIGHT	1538 mm
PRODUCT WIDTH	1037 mm
PRODUCT WEIGHT	820 kg
CERTIFICATIONS	C-Tick RoHS, ISO 9001 UL UL File No.: E134360 UkrSEPRO CE CUL
	Safety requirements: IEC/EN 61800-5 EAC IEC/EN 61800-3 Specification for general requirements: IEC/EN 61800-2 UL Category Control No.: NMMS, NMMS7

<b>FEATURES</b>	Externally accessible fan Temperature-controlled fan
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Brake chopper DC link choke Radio interference suppression filter Multi-line graphic display IGBT inverter Internal DC link Additional PCB protection Breaking resistance Control unit PC connection

<b>MCAD MODEL</b>	<a href="#">dg1_18.stp</a> <a href="#">dg1_18.dwg</a>
	<a href="#">eaton-profinet-de1-dc1-da1-dg1-dm1-dx1-mn040062-en-en.pdf</a>

<b>POLLUTION DEGREE</b>	2
<b>CLIMATIC PROOFING</b>	< 95 average relative humidity (RH), no condensation, no corrosion
<b>CONNECTION TO SMARTWIRE-DT</b>	Yes In conjunction with DXG-NET-SWD SmartWire DT module
<b>OPERATING MODE</b>	Sensorless vector control (SLV) Speed control with slip compensation U/f control Torque regulation
<b>FRAME SIZE</b>	FS8
<b>AIR VOLUME CAPACITY</b>	2800 m³/h
<b>ALTITUDE</b>	Max. 1000 m Max. 2000 m Above 1000 m with 1 % derating per 100 m
<b>ENVIRONMENTAL CLASS</b>	3C2, 3S2 (Air quality)
<b>APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED</b>	Yes
<b>MAINS SWITCH-ON FREQUENCY</b>	Maximum of one time every 60 seconds
<b>APPLICATION IN INDUSTRIAL AREA PERMITTED</b>	Yes
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	50 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN</b>	-10 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	-40 °C
<b>APPARENT POWER AT 600 V</b>	613.1 kVA
<b>APPARENT POWER AT 690 V</b>	705.1 kVA

<b>MOUNTING POSITION</b>	Vertical
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	65 kA
<b>RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE</b>	10 %
<b>RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE</b>	10 %
<b>PROTECTION</b>	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
<b>RATED OPERATIONAL POWER AT 525 V, 50 HZ</b>	355 kW
<b>RATED OPERATIONAL POWER AT 525 V, 50 HZ, 110% OVERLOAD</b>	400 kW
<b>RATED OPERATIONAL POWER AT 600 V, 50 HZ</b>	400 kW
<b>RATED OPERATIONAL POWER AT 600 V, 50 HZ, 110% OVERLOAD</b>	450 kW
<b>RESOLUTION</b>	0.01 Hz (Frequency resolution, setpoint value)
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	291 W
<b>SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR</b>	1050 VDC
<b>VOLTAGE RATING - MAX</b>	690 VAC
<b>OVERVOLTAGE CATEGORY</b>	III
<b>COMMUNICATION INTERFACE</b>	PROFIBUS, optional DeviceNet, optional CANopen®, optional Modbus RTU, built in Modbus TCP, built in BACnet MS/TP, built in SmartWire-DT, optional Ethernet IP, built in
<b>CONVERTER TYPE</b>	U converter
<b>DEGREE OF PROTECTION</b>	IP00 NEMA Other
<b>PROTOCOL</b>	BACnet CAN DeviceNet

	EtherNet/IP MODBUS Other bus systems PROFIBUS PROFINET IO TCP/IP
<b>ASSIGNED MOTOR CURRENT IM AT 525 V, 50 HZ, 110% OVERLOAD</b>	547 A
<b>ASSIGNED MOTOR CURRENT IM AT 525 V, 50 HZ, 150% OVERLOAD</b>	495.2 A
<b>ASSIGNED MOTOR CURRENT IM AT 600 V, 50 HZ, 110% OVERLOAD</b>	535 A
<b>ASSIGNED MOTOR CURRENT IM AT 600 V, 50 HZ, 150% OVERLOAD</b>	486 A
<b>ASSIGNED MOTOR CURRENT IM AT 690 V, 60 HZ, 110% OVERLOAD</b>	550 A
<b>ASSIGNED MOTOR CURRENT IM AT 690 V, 60 HZ, 150% OVERLOAD</b>	500 A
<b>SYSTEM CONFIGURATION TYPE</b>	TN-S, TN-C, TN-C-S, TT, IT
<b>ELECTROMAGNETIC COMPATIBILITY</b>	1st and 2nd environments (according to EN 61800-3)
<b>ASSIGNED MOTOR POWER AT 690 V, 60 HZ</b>	650 HP
<b>ASSIGNED MOTOR POWER AT 690 V, 60 HZ, 110% OVERLOAD</b>	700 HP
<b>BRAKING RESISTANCE</b>	2.5 $\Omega$
<b>EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID</b>	11486 W
<b>INPUT CURRENT ILN AT 110% OVERLOAD</b>	597 A
<b>INPUT CURRENT ILN AT 150% OVERLOAD</b>	527 A
<b>MAINS CURRENT DISTORTION</b>	28 %
<b>CURRENT LIMITATION</b>	0.1 - 2 x IH (CT), motor, main circuit
<b>NUMBER OF SLOTS</b>	2 (expansion)
<b>BRAKING TORQUE</b>	Adjustable to 150 %, DC - Main circuit Max. 30 % MN, Standard -

	Main circuit Max. 100 % of rated operational current $I_e$ with external braking resistor - Main circuit Adjustable to 150 % ( $I/I_e$ ), DC - Main circuit
<b>CABLE LENGTH</b>	200 m, screened, maximum permissible, Motor feeder $C3 \leq 10$ m, Radio interference level, maximum motor cable length
<b>FUNCTIONS</b>	4-quadrant operation possible
<b>OUTPUT VOLTAGE (U2)</b>	690 V AC, 3-phase 600 V AC, 3-phase
<b>NUMBER OF INPUTS (ANALOG)</b>	2
<b>NUMBER OF INPUTS (DIGITAL)</b>	8
<b>RADIO INTERFERENCE CLASS</b>	C1: with external filter, for conducted emissions only C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments
<b>NUMBER OF OUTPUTS (DIGITAL)</b>	1
<b>STARTING CURRENT - MAX</b>	200 %, $I_H$ , max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
<b>NUMBER OF PHASES (INPUT)</b>	3
<b>NUMBER OF RELAY OUTPUTS</b>	3 (parameterizable, 2 changeover contacts and 1 N/O, 6 A (240 V AC) / 6 A (24 V DC))
<b>NUMBER OF PHASES (OUTPUT)</b>	3

<b>RATED CONTROL SUPPLY VOLTAGE</b>	10 V DC (Us, max. 10 mA)
<b>EFFICIENCY</b>	98.1 % ( $\eta$ )
<b>RATED CONTROL VOLTAGE (UC)</b>	24 V DC (external, max. 250 mA options incl.)
<b>SUPPLY FREQUENCY</b>	50/60 Hz
<b>MAINS VOLTAGE - MAX</b>	600 V
<b>MAINS VOLTAGE - MIN</b>	525 V
<b>NOMINAL OUTPUT CURRENT I2N</b>	520 A
<b>NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)</b>	1
<b>NUMBER OF HW-INTERFACES (OTHER)</b>	1
<b>NUMBER OF HW-INTERFACES (PARALLEL)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-232)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-422)</b>	0
<b>NUMBER OF HW-INTERFACES (RS-485)</b>	1
<b>NUMBER OF HW-INTERFACES (SERIAL TTY)</b>	0
<b>NUMBER OF HW-INTERFACES (USB)</b>	0
<b>NUMBER OF INTERFACES (PROFINET)</b>	0
<b>NUMBER OF OUTPUTS (ANALOG)</b>	2
<b>OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	373 kW
<b>OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX</b>	448 kW
<b>OUTPUT FREQUENCY - MAX</b>	400 Hz
<b>OUTPUT FREQUENCY - MIN</b>	0 Hz
<b>OUTPUT VOLTAGE - MAX</b>	600 V
<b>OVERLOAD CURRENT IL AT 110% OVERLOAD</b>	649 A
<b>OVERLOAD CURRENT IL AT 150% OVERLOAD</b>	780 A
<b>SHOCK RESISTANCE</b>	UPS drop test (for weights

	inside the UPS frame) Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 Storage and transportation: maximum 15 g, 11 ms (inside the packaging)
<b>SUITABLE FOR</b>	Branch circuits, (UL/CSA)
<b>SWITCHING FREQUENCY</b>	2 kHz, 1.5 - 6 kHz adjustable, fPWM, Power section, Main circuit
<b>RATED OPERATIONAL VOLTAGE</b>	600 V AC, 3-phase 690 V AC, 3-phase
<b>SHORT-CIRCUIT PROTECTION RATING</b>	2 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
<b>VIBRATION</b>	Resistance: 5 - 15.8 Hz, Amplitude 1 mm (peak) Resistance: 5 - 150 Hz, According to EN 61800-5- 1, IEC/EN 60068-2-6 Resistance: 15.8 – 150 Hz, 1 g, Maximum acceleration amplitude
<b>RATED FREQUENCY - MAX</b>	66 Hz
<b>RATED FREQUENCY - MIN</b>	45 Hz
<b>RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD</b>	590 A
<b>RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD</b>	520 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	520 A
<b>SAFETY FUNCTION/LEVEL</b>	STO (Safe Torque Off, SIL1, PLc Cat 1)



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

