




## Eaton 5S1000LCD

Not for sale or distribution in Colorado, Vermont or Washington state - Eaton 5S UPS, Line-interactive UPS 1000VA/600W

□□□□

<b>PRODUCT NAME</b>	Eaton 5S UPS
<b>CATALOG NUMBER</b>	5S1000LCD
<b>UPC</b>	743172043559
<b>PRODUCT LENGTH/DEPTH</b>	3.4 in
<b>PRODUCT HEIGHT</b>	9.8 in
<b>PRODUCT WIDTH</b>	15 in
<b>PRODUCT WEIGHT</b>	21.7 lb
<b>COMPLIANCES</b>	FCC Part 15
<b>CERTIFICATIONS</b>	UL 497A CSA Std. C22.2 No. 107.1-01 ICES-003 VCCI UL 1778

□□□□	
TOPOLOGY	Line-interactive
FORM FACTOR	Tower
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	1000 VA
WATTAGE	330W
PACKAGE CONTENTS	<ul style="list-style-type: none"> <li>• UPS</li> <li>• USB cable</li> <li>• User manual</li> <li>• Important safety instructions</li> <li>• Limited warranty</li> </ul>
SURGE PROTECTION	Yes
INPUT CONNECTION	5-15P
INPUT CORD LENGTH	6 ft
INPUT NOMINAL VOLTAGE	120V
INPUT FREQUENCY RANGE	46-70 Hz (50 Hz system); 57-70 Hz (60 Hz system)
RECEPTACLE	(10) 5-15R
NUMBER OF OUTPUTS 5-15R	10
OUTPUT NOMINAL VOLTAGE	100/120/127V
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Not available
STANDARD FACTORY WARRANTY	<ul style="list-style-type: none"> <li>• 2-YEAR FACTORY WARRANTY</li> <li>• -2 years</li> <li>• -Parts, electronics, and batteries coverage</li> <li>• -Standard ground shipping</li> <li>• -Technical support</li> </ul>
EXTENDED SERVICE PLANS	<ul style="list-style-type: none"> <li>• ADVANCED DEPOT EXCHANGE</li> <li>• -5-YEAR DEPOT</li> </ul>



REPAIR: 5SW5Y-1400UC

- -Expedited parts coverage for 5 years
- -Parts, electronics and UPS batteries coverage
- -Next business day shipping
- -Technical support

COMMUNICATION	USB HID port as standard, 6-ft USB cable included
SOFTWARE COMPATIBILITY	Eaton UPS Companion software
USER INTERFACE	LCD display
NOISE LEVEL	<25 dB at 1 meter
RELATIVE HUMIDITY	0-93% non-condensing
TEMPERATURE RANGE	0° to 35°C (32° to 95°F)
EFFICIENCY AT MAX. LOAD	95
INPUT VOLTAGE RANGE	93-138 Vac
QUANTITY	1

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

