

Eaton 5S700I

Eaton 5S UPS, 700 VA, 420 W, Input: C14,
Outputs: (3) C13, (3) C13 surge only, Tower

PRODUCT NAME	Eaton 5S UPS
CATALOG NUMBER	5S700I
UPC	743172436894
PRODUCT LENGTH/DEPTH	260 mm
PRODUCT HEIGHT	250 mm
PRODUCT WIDTH	87 mm
PRODUCT WEIGHT	5.93 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 CE EAC

SPECIAL FEATURES

- Automatic Voltage Regulation (AVR)
- Saves space with a compact design that can be installed as a tower or under a computer monitor
- HID-compliant USB port (cable supplied), for automatic integration with major operating systems (Windows/Mac OS/Linux)
- Data line protection to ensure that the internet line (including xDSL) is protected against surges
- Easy to replace battery helps to extend UPS service life

TOPOLOGY	Line-interactive
FORM FACTOR	Tower
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	700 VA
WATTAGE	420 W
RACK MOUNTING KIT	No

PACKAGE CONTENTS

- (2) IEC-IEC cables
- USB cable
- User manual
- Safety instructions

SURGE PROTECTION	Yes
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	46 Hz
INPUT CONNECTION	C14

INPUT NOMINAL VOLTAGE	230V default (220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	46-70 Hz
RECEPTACLE	(3) C13, (3) C13 surge only
NUMBER OF OUTPUTS C13	6
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	Replaceable batteries, Automatic battery test, deep-discharge protection, cold-start capable
BATTERY REPLACEMENT	User replaceable
BATTERY RATING	12 V / 7 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	No
RUNTIME AT HALF LOAD	8.5 min
COMMUNICATION	USB port (HID compliant)
EXPANSION SLOTS	No
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton UPS Companion (enables safe system shutdown, energy usage metering and configuration of UPS settings)
USER INTERFACE	LEDs
TYPE OF INTERFACE	USB
POTENTIAL FREE SWITCH CONTACT	No
ALTITUDE	2000 m
NOISE LEVEL	<25 dB at 1 meter
RELATIVE HUMIDITY	0-85% non-condensing
TEMPERATURE RANGE	0° to 35°C (32° to 95°F)
OPERATING TEMPERATURE - MAX	35 °C

OPERATING TEMPERATURE - MIN	0 °C
OUTPUT APPARENT POWER	700 VA
INPUT VOLTAGE - MAX	275 V
INPUT VOLTAGE - MIN	175 V
OUTPUT VOLTAGE - MAX	276 V
OUTPUT VOLTAGE - MIN	184 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	1
EFFICIENCY AT MAX. LOAD	97
INPUT VOLTAGE RANGE	175-275 V
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.6
OUTPUT VOLTAGE RANGE	184-276 V
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	2 min
POWER CONSUMPTION	21 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

