



□□□□□

Eaton 630CFMM

Fuse-link, High Speed, 630 A, AC 690 V, DC 450 V, BS88, 38 x 136 mm, aR, BS

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	630CFMM
PRODUCT LENGTH/DEPTH	136 mm
PRODUCT HEIGHT	38 mm
PRODUCT WIDTH	83 mm
PRODUCT WEIGHT	329 g
COMPLIANCES	CE RoHS Compliant
CERTIFICATIONS	BS88 IEC 60269 UL Recognized

□□□□

□□

AMPERAGE RATING	630 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	450 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	110 mm
MOUNTING DIMENSION	M10
CURRENT TYPE	AC/DC
CLASS	Class aR
CLEARING (I ₂ T)	180000
WATT LOSSES	100 W
FUSE SHAPE	Offset slotted bolted tags
PRE ARC (I ₂ T)	45000
COLOR	None
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V AC
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	CFMM
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

