

## Eaton 40071352917

Eaton LED drivers including CG-S modules  
LED supply and monitoring module V-CG-  
SLU 700 (without packing)

<b>PRODUCT NAME</b>	Eaton LED drivers including CG-S modules
<b>CATALOG NUMBER</b>	40071352917
<b>PRODUCT LENGTH/DEPTH</b>	139 mm
<b>PRODUCT HEIGHT</b>	21 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	0.061 kg
<b>CERTIFICATIONS</b>	CE marking

LAMP TYPE	LED
NOMINAL VOLTAGE - MAX	240 V
NOMINAL VOLTAGE - MIN	220 V
PROTECTION CLASS	I or II
NOMINAL VOLTAGE RANGE DC - MAX	275 V
NOMINAL VOLTAGE RANGE DC - MIN	176 V
ADDITIONAL DATA LINE NEEDED	No
AMBIENT TEMPERATURE - MAX	50 °C
AMBIENT TEMPERATURE - MIN	-20 °C
CONNECTION TERMINALS (IN)	2.5 mm <sup>2</sup>
CONNECTION TERMINALS (OUT)	1.5 mm <sup>2</sup>
CONSTANT OUTPUT	Constant current output
CURRENT CONSUMPTION AT 220V DC	56 mA
ENEC CERTIFIED	Yes
ENERGY-EFFICIENCY INDEX	A2
HOUSING COLOR	Grey
HOUSING MATERIAL	Flame retardant polycarbonate
INRUSH CURRENT	3 A
LED MODULE LOAD (NUMBER OF LEDS)	1-4 LEDs (rated current 700 mA), series connection (UF = 2,85 ... 3,5 V)
LUMINOUS FLUX $\Phi_E/\Phi_{IN}$ AT THE END OF RATED OPERATING TIME	100 %
MAXIMAL NUMBER OF MONITORED LUMINAIRES PER CIRCUIT	20
REVERSE-POLARITY PROTECTED TERMINALS (IN)	Yes
SLI-TECHNOLOGY	No
PRODUCT BRANDING	Eaton

<b>DEGREE OF PROTECTION (IP)</b>	IP20
<b>MAXIMAL PERMISSIBLE TEST POINT TEMPERATURE</b>	70 °C
<b>LINE LENGTH - MAX</b>	1 m
<b>OUTPUT POWER - MAX</b>	9.8 W
<b>OPERATING FREQUENCY</b>	60 Hz
<b>OUTPUT CURRENT - MAX</b>	700 mA
<b>OUTPUT VOLTAGE - MAX</b>	14 VDC
<b>POWER CONSUMPTION MAINS OPERATION - APPARENT POWER (VA)</b>	21.4 VA
<b>POWER FACTOR</b>	.61
<b>STANDBY POWERLOSS AT 230 V / 50 HZ</b>	0.7 W
<b>SUITABLE FOR CONSTANT CURRENT</b>	YES
<b>SUITABLE FOR CONSTANT VOLTAGE</b>	NO
<b>SUITABLE FOR DC-VOLTAGE (PRIMARY SIDE)</b>	YES
<b>CONSTANT LIGHT OUTPUT (CLO)</b>	YES
<b>IFTTT SUPPORT AVAILABLE</b>	NO
<b>DIMMING 0-10 V</b>	NO
<b>DIMMING 1-10 V</b>	NO
<b>DIMMING DALI</b>	NO
<b>DIMMING DMX</b>	NO
<b>DIMMING POTENTIOMETER (INTEGRATED)</b>	NO
<b>DIMMING LINESWITCH</b>	NO
<b>DIMMING MANUFACTURER'S PROPRIETARY SYSTEM</b>	NO
<b>DIMMING MAINS VOLTAGE MODULATION</b>	NO
<b>DIMMING PHASE CUT-OFF</b>	NO
<b>DIMMING PHASE CUT-ON</b>	NO
<b>DIMMING PROGRAMMABLE</b>	NO
<b>DIMMING RF</b>	NO
<b>DIMMING SINE WAVE</b>	NO

<b>REDUCTION</b>	
<b>POWER CONSUMPTION</b>	13 W
<b>SUITABLE FOR OUTDOOR USE</b>	NO
<b>DIMMING TOUCH AND DIM</b>	NO
<b>DIMMING ZIGBEE</b>	NO
<b>DIMMING WITH PUSH-BUTTON</b>	NO
<b>DIMMING DSI</b>	NO
<b>OPERATION BY BLUETOOTH</b>	NO
<b>COMPATIBLE WITH APPLE HOMEKIT</b>	NO
<b>COMPATIBLE WITH GOOGLE ASSISTANT</b>	NO
<b>COMPATIBLE WITH AMAZON ALEXA</b>	NO
<b>COMPATIBLE WITH CASAMBI</b>	NO
<b>HOUSING</b>	Plastic housing
<b>PROTECTION CLASS ACCORDING TO IEC 61140</b>	None
<b>OUTPUT VOLTAGE - MIN</b>	14 V
<b>NO DIM FUNCTION</b>	YES
<b>MODEL</b>	Static

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

