



Eaton 40071353262

Eaton GuideLed mounting set for 11812, Exit sign, 30m, Recessed wall mounting, CGLine + technology, LED, Maintained / Non-Maintained operation, IP20, 1h/3h/8h selectable duration, requires LED panel

□□□□

PRODUCT NAME	Eaton GuideLed SC Emergency Luminaire
CATALOG NUMBER	40071353262
PRODUCT LENGTH/DEPTH	295 mm
PRODUCT HEIGHT	45 mm
PRODUCT WIDTH	115 mm
PRODUCT WEIGHT	0.58 kg
CERTIFICATIONS	CE

BATTERY VOLTAGE	3.7 V
BATTERY QUALITY	Lithium-ion
GLOW WIRE TEST	850 °C
PROTECTION CLASS	II
OUTDOOR USE COMPLIANCE	False
EXPLOSION PROTECTED	False
DEGREE OF PROTECTION	IP20
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	False
LAMP HOLDER	Other
TYPE OF INDICATOR	Only single-sided
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Peripheral (individual battery)
VOLTAGE TYPE	AC
POWER FACTOR	0.88
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	True
RESERVE-POLARITY PROTECTED	True
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	4.7 W
RATED LIFE TIME L70/B50 AT 25 °C	50000 hour
RATED LIFE TIME L90/B10 AT 25 °C	50000 hour
TYPE OF CONTROL GEAR	LED operating device voltage-controlled
TYPE OF WIRING	Suitable for through wiring
NOMINAL VOLTAGE AC - MAX	240 V
NOMINAL VOLTAGE AC - MIN	220 V
APPARENT POWER AT MAINS	5.3 VA

OPERATION(50CD)	
EFFECTIVE POWER AT MAINS OPERATION (50CD)	4.7 W
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	0 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	30 °C
NOMINAL OPERATION TIME - MIN	1 hour
NOMINAL OPERATION TIME - MAX	8 hour
AUTONOMY	1/3/8 hours
SUITABLE FOR STANDBY SWITCHING	Yes
SUITABLE FOR CONTINUOUS CIRCUIT	Yes
RAL-NUMBER (SIMILAR) HOUSING	7025
MOUNTING METHOD	Surface mounting/recessed mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	Grey
MATERIAL COVER	Plastic, opal
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	False
BUILT-IN LENGTH	295 mm
BUILT-IN WIDTH	115 mm
BUILT-IN HEIGHT/DEPTH	2 mm
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK03
KIND OF LUMINAIRE	Exit sign luminaire
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	115 lm
LIGHT DISTRIBUTOR	Diffuser lens/optic/panel
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route signage
COLOR OF LIGHT	White
COLOR RENDERING INDEX (CRI)	70-79
NUMBER OF LIGHTING HEADS	1
VIEWING DISTANCE	30 m

DATA CONNECTION TERMINAL	1.5 mm ²
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	2.5mm ²
TESTING SYSTEM	CGLine +
WITH REMOTE CONTROL	No

□□□□:
□□□□:
□□□:
□□: