



□□□□□

Eaton 40071353610

Eaton Ceiling mounting set 10021 CG-S with canopy, incl. LED supply (V-CG-SLS28) and CG-S technology (20 addresses), 20m, without pictogram

□□□□

PRODUCT NAME	Eaton GuideLed CG-S Emergency luminaire
CATALOG NUMBER	40071353610
PRODUCT LENGTH/DEPTH	225 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	0.18 kg
CERTIFICATIONS	CE

BATTERY QUALITY	Not applicable
PERMISSIBLE AMBIENT TEMPERATURE - MIN	-20 °C
PERMISSIBLE AMBIENT TEMPERATURE - MAX	40 °C
PROTECTION CLASS	II
DEGREE OF IMPACT RESISTANCE (IK)	IK 03
OUTDOOR USE COMPLIANCE	False
EXPLOSION PROTECTED	False
DEGREE OF PROTECTION	IP40
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	False
LAMP HOLDER	None
TYPE OF INDICATOR	Single/double-sided
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Central (central battery)
VOLTAGE TYPE	AC/DC
CURRENT CONSUMPTION AT 220V DC	12 mA
APPARENT POWER AT MAINS OPERATION	5.5 VA
EFFECTIVE POWER AT MAINS OPERATION	2.9 W
POWER FACTOR	0.5
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	True
RESERVE-POLARITY PROTECTED	True
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	2.9 W
RATED LIFE TIME L70/B50 AT 25 °C	50000 hour
TYPE OF CONTROL GEAR	LED operating device

	voltage-controlled
TYPE OF WIRING	Ending
NOMINAL VOLTAGE AC - MAX	240 V
NOMINAL VOLTAGE AC - MIN	220 V
NOMINAL VOLTAGE DC	220 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	-20 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	40 °C
INRUSH CURRENT	1.5
SUITABLE FOR STANDBY SWITCHING	Yes
SUITABLE FOR CONTINUOUS CIRCUIT	Yes
RAL-NUMBER (SIMILAR) HOUSING	7025
MOUNTING METHOD	Ceiling surface mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	Light grey, RAL 7035
MATERIAL COVER	Without cover
LABELLING TYPE	Acrylic plate
PICTOGRAM INCLUDED	False
NUMBER OF POLES (NUMERIC)	2
IMPACT STRENGTH	IK03
KIND OF LUMINAIRE	Exit sign luminaire
LIGHT DISTRIBUTOR	Diffuser lens/optic/panel
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route signage
VIEWING DISTANCE	20 m
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	Plug-in connection
OPERATING VOLTAGE - MAX	240 V
OPERATING VOLTAGE - MIN	220 V
TECHNOLOGY	LED
APPLICATION	Acc. DIN 4844
SUITABLE FOR	Emergency Lighting
POWER CONSUMPTION MAINS OPERATION - EFFECTIVE POWER (W)	2.9 W

POWER CONSUMPTION	
MAINS OPERATION - APPARENT POWER (VA)	5.5 VA
LIGHT OUTPUT EXIT SIGN LUMINAIRE	Double sided
TESTING SYSTEM	CG technology STAR technology STAR+ technology
WITH REMOTE CONTROL	No
