



Eaton 40071354593

Eaton CrystalWay 19022 CG-S, Escape sign-disc luminaire 30 m, for wall and ceiling mounting, incl. set of pictograms (arrow right, left, down, up, blind)

□□□□

PRODUCT NAME	Eaton CrystalWay CPS Emergency luminaire
CATALOG NUMBER	40071354593
PRODUCT LENGTH/DEPTH	331 mm
PRODUCT HEIGHT	183 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.953 kg
CERTIFICATIONS	CE

BATTERY QUALITY	Not applicable
PERMISSIBLE AMBIENT TEMPERATURE - MIN	-20 °C
PERMISSIBLE AMBIENT TEMPERATURE - MAX	40 °C
PROTECTION CLASS	I
DEGREE OF IMPACT RESISTANCE (IK)	IK 04
OUTDOOR USE COMPLIANCE	False
EXPLOSION PROTECTED	False
DEGREE OF PROTECTION	IP42
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	True
TYPE OF INDICATOR	Single/double-sided
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Central (central battery)
VOLTAGE TYPE	AC/DC
CURRENT CONSUMPTION AT 220V DC	15 mA
APPARENT POWER AT MAINS OPERATION	6.5 VA
EFFECTIVE POWER AT MAINS OPERATION	3.7 W
POWER FACTOR	0.6
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	True
RESERVE-POLARITY PROTECTED	True
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	3.7 W
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
NOMINAL VOLTAGE AC - MAX	240 V
NOMINAL VOLTAGE AC -	220 V

MIN	
NOMINAL VOLTAGE DC	275 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	-20 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	40 °C
INRUSH CURRENT	1.5
MOUNTING METHOD	Wall surface mounted / ceiling surface mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	White
MATERIAL COVER	Plastic, transparent
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	Yes
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK04
KIND OF LUMINAIRE	Exit sign luminaire
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	60 lm
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route signage
VIEWING DISTANCE	30 m
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	Plug-in connection
PRODUCT BRANDING	Eaton
OPERATING VOLTAGE - MAX	240 V
OPERATING VOLTAGE - MIN	220 V
TECHNOLOGY	LED
APPLICATION	Acc. DIN 4844
SUITABLE FOR	Emergency Lighting
POWER CONSUMPTION MAINS OPERATION - EFFECTIVE POWER (W)	3.7 W
POWER CONSUMPTION MAINS OPERATION - APPARENT POWER (VA)	6.5 VA
LIGHT OUTPUT EXIT SIGN LUMINAIRE	Double sided
TESTING SYSTEM	CG technology STAR technology STAR+ technology

100 %

00:

