

Eaton 40071354891

Eaton Atlantic LED D CG-S, double-sided,
IP65, without Insert pictograms (2 required)

PRODUCT NAME	Eaton Atlantic LED CG-S Emergency luminaire
CATALOG NUMBER	40071354891
PRODUCT LENGTH/DEPTH	303 mm
PRODUCT HEIGHT	166 mm
PRODUCT WIDTH	136 mm
PRODUCT WEIGHT	1.3 kg
CERTIFICATIONS	CE

BATTERY QUALITY	Not applicable
PERMISSIBLE AMBIENT TEMPERATURE - MIN	-20 °C
PERMISSIBLE AMBIENT TEMPERATURE - MAX	40 °C
PROTECTION CLASS	I
DEGREE OF IMPACT RESISTANCE (IK)	IK 10
OUTDOOR USE COMPLIANCE	True
EXPLOSION PROTECTED	False
DEGREE OF PROTECTION	IP65
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	True
LAMP HOLDER	None
LAMP POWER	3 W
TYPE OF INDICATOR	Double-sided
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Central (central battery)
VOLTAGE TYPE	AC/DC
CURRENT CONSUMPTION AT 220V DC	21.5 mA
APPARENT POWER AT MAINS OPERATION	8.5 VA
EFFECTIVE POWER AT MAINS OPERATION	5 W
POWER FACTOR	.59
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	True
RESERVE-POLARITY PROTECTED	True
ENERGY EFFICIENCY CLASS	A
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Screw connection
MAX. SYSTEM POWER	5 W



RATED LIFE TIME L70/B50 AT 25 °C	50000 hour
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
NOMINAL VOLTAGE AC - MAX	240 V
NOMINAL VOLTAGE AC - MIN	220 V
NOMINAL VOLTAGE DC	220 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	-20 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	40 °C
INRUSH CURRENT	1.5
SUITABLE FOR STANDBY SWITCHING	Yes
SUITABLE FOR CONTINUOUS CIRCUIT	Yes
RAL-NUMBER (SIMILAR) HOUSING	7001
MOUNTING METHOD	Ceiling surface mounting
MATERIAL HOUSING	Aluminium
COLOR HOUSING	Grey
MATERIAL COVER	Plastic, transparent
LIMITED SURFACE TEMPERATURE	True
LABELLING TYPE	Insert sheet/plate
PICTOGRAM INCLUDED	False
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK10
KIND OF LUMINAIRE	Exit sign luminaire
LIGHT DISTRIBUTOR	Diffuser lens/optic/panel
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route signage
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	True
VIEWING DISTANCE	24 m
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	Screw connection

OPERATING VOLTAGE - MAX	240 V
OPERATING VOLTAGE - MIN	220 V
TECHNOLOGY	LED
APPLICATION	Acc. DIN 4844
SUITABLE FOR	Emergency Lighting
POWER CONSUMPTION MAINS OPERATION - EFFECTIVE POWER (W)	5 W
POWER CONSUMPTION MAINS OPERATION - APPARENT POWER (VA)	8.5 VA
LIGHT OUTPUT EXIT SIGN LUMINAIRE	Double sided
TESTING SYSTEM	CG technology STAR technology STAR+ technology
WITH REMOTE CONTROL	No

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

