



Eaton 400NHG2B-400

Eaton Bussmann series Fuse-link, LV, 400 A, AC 400 V, NH2, gL/gG, IEC, dual indicator, live gripping lugs

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage NH Fuse
CATALOG NUMBER	400NHG2B-400
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	71 mm
PRODUCT WIDTH	54 mm
PRODUCT WEIGHT	669 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	IEC 60269-1 IEC 60269-2 DIN 43620

□□□□

AMPERAGE RATING	400 A
FITTED WITH:	Metal gripping lugs
FUSE SIZE	NH2
CURRENT TYPE	AC
BREAKING CAPACITY	120 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED SWITCHING CAPACITY	120 kA
RATED VOLTAGE AC	400 V
CLASS	Class gG/gL
FUSE TYPE	Square body with knife blade contact
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
ACCESSORY/SPARE PART TYPE	SDL-2 Solid link FEH- Fuse extraction handle SD12-SK Shroud kit SD12-PB 2-phase barriers and 2 ganging links TD2-IP20 Triple pole protection kit
COLOR	None
INTERRUPT RATING	120 kAIC
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	24 W
CONNECTION	Blade end
CONSTRUCTION	NH2
CONSTRUCTION SIZE	NH2
FUSE SHAPE	Square body Knife blade contacts
VOLTAGE TYPE	AC
SUITABLE FOR	SD2-D Single pole NH Fuse base Microswitch 170H0235 Microswitch 170H0236 EBH Size 00 to 4 Horizontal fuse switch-disconnectors TD2-D Triple pole NH Fuse base

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250967en.pdf](#)

MATERIAL	Ceramic body
QUANTITY	3
VOLTAGE RATING	400 V
TYPE	Fuse
APPLICATION	• industrial • Utilities, Solar, Wind
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system A
RATED SWITCHING CAPACITY AC	120 kA

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

