



## Eaton 400P09C

Eaton Bussmann series low voltage british standard fuse, 400A, AC 600 V, DC 250 V, HRCII-MISC, 59 x 136 mm, gL/gG, CSA

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	400P09C
<b>UPC</b>	051712551205
<b>PRODUCT LENGTH/DEPTH</b>	136 mm
<b>PRODUCT HEIGHT</b>	59 mm
<b>PRODUCT WIDTH</b>	59 mm
<b>PRODUCT WEIGHT</b>	0.9 g
<b>COMPLIANCES</b>	RoHS Compliant



Powering Business Worldwide

□□□□

<b>AMPERAGE RATING</b>	400 A
<b>CONSTRUCTION TYPE</b>	HRCII-MISC
<b>CURRENT TYPE</b>	AC/DC
<b>MOUNTING DIMENSION</b>	M8
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	113 mm
<b>BREAKING CAPACITY</b>	200 kA
<b>FREQUENCY RATING - MAX</b>	50 Hz
<b>RATED SWITCHING CAPACITY</b>	200 kA
<b>RATED VOLTAGE AC</b>	600 V
<b>RATED VOLTAGE DC</b>	250 V
<b>CLASS</b>	Class gG/gL
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>COLOR</b>	None
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>CONNECTION</b>	Bolt-on
<b>CONSTRUCTION SIZE</b>	Other
<b>FUSE SHAPE</b>	Center bolted tags
<b>VOLTAGE TYPE</b>	AC/DC
<b>MATERIAL</b>	Ceramic body
<b>VOLTAGE RATING</b>	600 V
<b>TYPE</b>	Canadian fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

□□

