

Eaton 9701-3101-00P

Eaton DG1 Variable frequency drive, 230 V AC, 3-phase, 31 A, 7.5 kW, IP54/NEMA12, Brake chopper, DC link choke

PRODUCT NAME	Eaton DG1 variable frequency drive
CATALOG NUMBER	9701-3101-00P
PRODUCT LENGTH/DEPTH	265.1 mm
PRODUCT HEIGHT	558 mm
PRODUCT WIDTH	204.6 mm
PRODUCT WEIGHT	22 kg
CERTIFICATIONS	CE EAC UL508 IEC/EN61800-3 RoHS, ISO 9001 Safety requirements: IEC/EN 61800-5 UL File No.: E134360 UL report applies to both US and Canada C-Tick Certified by UL for use in Canada CUL Specification for general requirements: IEC/EN 61800-2 UkrSEPRO UL IEC/EN 61800-3 IEC/EN61800-5 CSA-C22.2 No. 274-13 UL Category Control No.: NMMS, NMMS7
CATALOG NOTES	The brake resistors are assigned based on the maximum rated power of the variable frequency drive. Additional brake resistors and designs (e.g. different duty cycles) are

PRODUCT CATEGORY	Variable frequency drives
FEATURES	<p>Temperature-controlled fan Tool-less swapping of fan Parameterization: Fieldbus</p> <p>Parameterization: Keypad Parameterization: Power Xpert inControl</p>
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.

eaton-profinet-de1-dc1-da1-dg1-dm1-dx1-mn040062-en-en.pdf
eaton-frequency-inverter-dg1-dimensions-003.eps eaton-frequency-inverter-dg1-3d-drawing-003.eps

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Control unit Radio interference suppression filter Brake chopper Internal DC link IGBT inverter Breaking resistance PC connection Additional PCB protection DC link choke Multi-line graphic display
POLLUTION DEGREE	2
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	In conjunction with DXG-NET-SWD SmartWire DT module Yes
OPERATING MODE	Speed control with slip

	compensation Torque regulation U/f control Sensorless vector control (SLV)
FRAME SIZE	FS3
AIR VOLUME CAPACITY	144 m ³ /h
ALTITUDE	Max. 3000 m Above 1000 m with 1 % derating per 100 m Max. 1000 m Max. 2000 m for Corner Grounded TN Systems
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-30 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 230 V	19.1 kVA
APPARENT POWER AT 240 V	20 kVA
ASSIGNED MOTOR CURRENT IM AT 220 - 240 V, 60 HZ, 150% OVERLOAD	28 A
ASSIGNED MOTOR CURRENT IM AT 230 V, 50 HZ, 110% OVERLOAD	38 A
ASSIGNED MOTOR	26.4 A

CURRENT IM AT 230 V, 50 HZ, 150% OVERLOAD	
ASSIGNED MOTOR CURRENT IM AT 230 V, 60 HZ, 110% OVERLOAD	42 A
MOUNTING POSITION	Vertical
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	100 kA
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
HEAT DISSIPATION DETAILS	Operation (with 150 % overload), allow for derating
RESOLUTION	0.01 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	18.15 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	425 VDC
VOLTAGE RATING - MAX	240 VAC
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	Modbus RTU, built in DeviceNet, optional CANopen®, optional SmartWire-DT, optional Modbus TCP, built in Ethernet IP, built in BACnet MS/TP, built in PROFIBUS, optional
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	NEMA 12 IP54
PROTOCOL	PROFINET IO MODBUS Other bus systems TCP/IP BACnet

	PROFIBUS CAN DeviceNet EtherNet/IP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	10 HP
SYSTEM CONFIGURATION TYPE	TN-S, TN-C, TN-C-S, TT, IT
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE, 110 % OVERLOAD	15 HP
BRAKING RESISTANCE	10 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	445 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 110% OVERLOAD	44.2 A
INPUT CURRENT ILN AT 150% OVERLOAD	28.7 A
MAINS CURRENT DISTORTION	30.8 %
CURRENT LIMITATION	0.1 - 2 x I _H (CT), motor, main circuit
NUMBER OF SLOTS	2 (expansion)
BRAKING TORQUE	Max. 30 % M _N , Standard - Main circuit Adjustable to 150 %, DC - Main circuit Max. 100 % of rated operational current I _e with external braking resistor - Main circuit Adjustable to 150 % (I/I _e), DC - Main circuit
CABLE LENGTH	C3 \leq 50 m, Radio interference level, maximum motor cable length 150 m, screened, maximum permissible, Motor feeder

	C2 ≤ 10 m, Radio interference level, maximum motor cable length
FUNCTIONS	4-quadrant operation possible
OUTPUT VOLTAGE (U2)	230 V AC, 3-phase 240 V AC, 3-phase
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	8
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments C1: with external filter, for conducted emissions only
NUMBER OF OUTPUTS (DIGITAL)	1
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	3 (parameterizable, 2 changeover contacts and 1 N/O, 6 A (240 V AC) / 6 A (24 V DC))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	445 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 10 mA)
EFFICIENCY	97.7 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 250 mA options incl.)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT	8.2 mA

GROUND IPE - MAX	
MAINS VOLTAGE - MAX	240 V
MAINS VOLTAGE - MIN	208 V
NOMINAL OUTPUT CURRENT I2N	31 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	1
NUMBER OF HW-INTERFACES (OTHER)	1
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	7.5 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	11 kW
OUTPUT FREQUENCY - MAX	400 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	240 V
OVERLOAD CURRENT IL AT 110% OVERLOAD	52.8 A
OVERLOAD CURRENT IL AT 150% OVERLOAD	46.5 A
SHOCK RESISTANCE	Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 Storage and transportation: maximum 15 g, 11 ms (inside the packaging)

	UPS drop test (for weights inside the UPS frame)
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	4 kHz, 1 - 12 kHz adjustable, fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	240 V AC, 3-phase 230 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	60 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
VIBRATION	Resistance: 15.8 – 150 Hz, 1 g, Maximum acceleration amplitude Resistance: 5 - 15.8 Hz, Amplitude 1 mm (peak) Resistance: 5 - 150 Hz, According to EN 61800-5-1, IEC/EN 60068-2-6
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD	48 A
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	31 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	31 A
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 1-PHASE	7.5 kW
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 3-PHASE, 110% OVERLOAD	11 kW
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL1, PLc Cat 1)
HEAT DISSIPATION AT CURRENT/SPEED	143 W at 25% current and 0% speed 165 W at 25% current and 50% speed 183 W at 100% current and 50% speed 204 W at 50% current and 50% speed 220 W at 50% current and 90% speed

308 W at 100% current
and 0% speed
367 W at 50% current and
0% speed
434 W at 100% current
and 90% speed

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

