

Eaton 9702-2002-00P

Eaton DG1 Variable frequency drive, 400 V
AC, 3-phase, 12 A, 5.5 kW, IP21/NEMA1,
Brake chopper, DC link choke

| | |
|-----------------------------|--|
| | |
| PRODUCT NAME | Eaton DG1 variable frequency drive |
| CATALOG NUMBER | 9702-2002-00P |
| PRODUCT LENGTH/DEPTH | 244.7 mm |
| PRODUCT HEIGHT | 419 mm |
| PRODUCT WIDTH | 167.8 mm |
| PRODUCT WEIGHT | 10.7 kg |
| CERTIFICATIONS | UL UL report applies to both US and Canada UkrSEPRO Certified by UL for use in Canada C-Tick UL File No.: E134360 IEC/EN 61800-3 EAC CE IEC/EN61800-5 CUL Specification for general requirements: IEC/EN 61800-2 IEC/EN61800-3 CSA-C22.2 No. 274-13 UL508 RoHS, ISO 9001 Safety requirements: IEC/EN 61800-5 UL Category Control No.: NMMS, NMMS7 |
| CATALOG NOTES | The brake resistors are assigned based on the maximum rated power of the variable frequency drive. Additional brake resistors and designs (e.g. different duty cycles) are |

| | |
|---|---|
| PRODUCT CATEGORY | Variable frequency drives |
| FEATURES | <p>Temperature-controlled fan</p> <p>Tool-less swapping of fan</p> <p>Parameterization: Fieldbus</p> <p>Parameterization: Keypad</p> <p>Parameterization: Power Xpert inControl</p> |
| 10.10 TEMPERATURE RISE | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 ELECTROMAGNETIC COMPATIBILITY | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 MECHANICAL FUNCTION | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |
| 10.2.2 CORROSION RESISTANCE | Meets the product standard's requirements. |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES | Meets the product standard's requirements. |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT | Meets the product standard's requirements. |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements. |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION | Meets the product standard's requirements. |
| 10.2.5 LIFTING | Does not apply, since the entire switchgear needs to be evaluated. |

| |
|---|
| eaton-profinet-de1-dc1-da1-dg1-dm1-dx1-mn040062-en-en.pdf |
| eaton-frequency-inverter-dg1-dimensions-002.eps |
| eaton-frequency-inverter-dg1-3d-drawing-002.eps |

| | |
|---|---|
| 10.2.6 MECHANICAL IMPACT | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 INSCRIPTIONS | Meets the product standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| FITTED WITH: | PC connection Radio interference suppression filter Internal DC link IGBT inverter Additional PCB protection Multi-line graphic display Breaking resistance Control unit Brake chopper DC link choke |
| POLLUTION DEGREE | 2 |
| CLIMATIC PROOFING | < 95 average relative humidity (RH), no condensation, no corrosion |
| CONNECTION TO SMARTWIRE-DT | In conjunction with DXG-NET-SWD SmartWire DT module Yes |
| OPERATING MODE | U/f control |

| | |
|---|--|
| | Torque regulation Speed control with slip compensation Sensorless vector control (SLV) |
| FRAME SIZE | FS2 |
| AIR VOLUME CAPACITY | 94 m ³ /h |
| ALTITUDE | Above 1000 m with 1 % derating per 100 m Max. 2000 m for Corner Grounded TN Systems Max. 3000 m Max. 1000 m |
| ENVIRONMENTAL CLASS | 3C2, 3S2 (Air quality) |
| APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED | Yes |
| MAINS SWITCH-ON FREQUENCY | Maximum of one time every 60 seconds |
| APPLICATION IN INDUSTRIAL AREA PERMITTED | Yes |
| AMBIENT OPERATING TEMPERATURE - MAX | 50 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -10 °C |
| AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX | 50 °C |
| AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN | -30 °C |
| AMBIENT STORAGE TEMPERATURE - MAX | 70 °C |
| AMBIENT STORAGE TEMPERATURE - MIN | -40 °C |
| APPARENT POWER AT 400 V | 11.1 kVA |
| APPARENT POWER AT 480 V | 13.9 kVA |
| ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 110% OVERLOAD | 15.2 A |
| ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD | 11.5 A |
| MOUNTING POSITION | Vertical |
| RATED CONDITIONAL | 100 kA |

| | |
|--|---|
| SHORT-CIRCUIT CURRENT (IQ) | |
| RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE | 10 % |
| RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE | 10 % |
| PROTECTION | Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4) |
| HEAT DISSIPATION DETAILS | Operation (with 150 % overload), allow for derating |
| RATED OPERATIONAL POWER AT 500 V, 50 HZ, 3-PHASE, 110% OVERLOAD | 7.5 kW |
| RESOLUTION | 0.01 Hz (Frequency resolution, setpoint value) |
| STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS | 15.75 W |
| SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR | 850 VDC |
| VOLTAGE RATING - MAX | 500 VAC |
| OVERVOLTAGE CATEGORY | III |
| COMMUNICATION INTERFACE | Modbus RTU, built in PROFIBUS, optional Ethernet IP, built in DeviceNet, optional CANopen®, optional Modbus TCP, built in BACnet MS/TP, built in SmartWire-DT, optional |
| CONVERTER TYPE | U converter |
| DEGREE OF PROTECTION | NEMA 1 IP21 |
| PROTOCOL | PROFINET IO Other bus systems CAN BACnet DeviceNet TCP/IP PROFIBUS MODBUS EtherNet/IP |

| | |
|--|--|
| ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD | 11 A |
| ASSIGNED MOTOR CURRENT IM AT 440/480 V, 60 HZ, 110% OVERLOAD | 14 A |
| ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 110% OVERLOAD | 12.1 A |
| ASSIGNED MOTOR CURRENT IM AT 500 V, 50 HZ, 150% OVERLOAD | 9 A |
| SYSTEM CONFIGURATION TYPE | TN-S, TN-C, TN-C-S, TT, IT |
| ELECTROMAGNETIC COMPATIBILITY | 1st and 2nd environments (according to EN 61800-3) |
| ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE | 7.5 HP |
| ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE, 110 % OVERLOAD | 10 HP |
| BRAKING RESISTANCE | 42 Ω |
| EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID | 191 W |
| HEAT DISSIPATION CAPACITY PDISS | 0 W |
| HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID | 0 W |
| INPUT CURRENT ILN AT 110% OVERLOAD | 15 A |
| INPUT CURRENT ILN AT 150% OVERLOAD | 11.2 A |
| MAINS CURRENT DISTORTION | 33.8 % |
| CURRENT LIMITATION | 0.1 - 2 x IH (CT), motor, main circuit |
| NUMBER OF SLOTS | 2 (expansion) |
| BRAKING TORQUE | Adjustable to 150 % (I/Ie), DC - Main circuit Max. 100 % of rated operational current Ie with external braking resistor - Main circuit Adjustable to 150 %, DC - |

| | |
|--|--|
| | Main circuit Max. 30 % MN, Standard - Main circuit |
| CABLE LENGTH | 150 m, screened, maximum permissible, Motor feeder C2 ≤ 10 m, Radio interference level, maximum motor cable length C3 ≤ 50 m, Radio interference level, maximum motor cable length |
| FUNCTIONS | 4-quadrant operation possible |
| OUTPUT VOLTAGE (U2) | 400 V AC, 3-phase 480 V AC, 3-phase 500 V AC, 3-phase |
| NUMBER OF INPUTS (ANALOG) | 2 |
| NUMBER OF INPUTS (DIGITAL) | 8 |
| RADIO INTERFERENCE CLASS | C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: with external filter, for conducted emissions only Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments |
| NUMBER OF OUTPUTS (DIGITAL) | 1 |
| STARTING CURRENT - MAX | 200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section |
| NUMBER OF PHASES (INPUT) | 3 |
| NUMBER OF RELAY OUTPUTS | 3 (parameterizable, 2 changeover contacts and 1 N/O, 6 A (240 V AC) / 6 A (24 V DC)) |
| NUMBER OF PHASES | 3 |

| | |
|---|---|
| (OUTPUT) | |
| POWER CONSUMPTION | 191 W |
| RATED CONTROL SUPPLY VOLTAGE | 10 V DC (Us, max. 10 mA) |
| EFFICIENCY | 98.2 % (η) |
| RATED CONTROL VOLTAGE (UC) | 24 V DC (external, max. 250 mA options incl.) |
| SUPPLY FREQUENCY | 50/60 Hz |
| LEAKAGE CURRENT AT GROUND IPE - MAX | 9 mA |
| MAINS VOLTAGE - MAX | 500 V |
| MAINS VOLTAGE - MIN | 380 V |
| NOMINAL OUTPUT CURRENT I2N | 12 A |
| NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET) | 1 |
| NUMBER OF HW-INTERFACES (OTHER) | 1 |
| NUMBER OF HW-INTERFACES (PARALLEL) | 0 |
| NUMBER OF HW-INTERFACES (RS-232) | 0 |
| NUMBER OF HW-INTERFACES (RS-422) | 0 |
| NUMBER OF HW-INTERFACES (RS-485) | 1 |
| NUMBER OF HW-INTERFACES (SERIAL TTY) | 0 |
| NUMBER OF HW-INTERFACES (USB) | 0 |
| NUMBER OF INTERFACES (PROFINET) | 0 |
| NUMBER OF OUTPUTS (ANALOG) | 2 |
| OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX | 5.5 kW |
| OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX | 7.5 kW |
| OUTPUT FREQUENCY - MAX | 400 Hz |
| OUTPUT FREQUENCY - MIN | 0 Hz |
| OUTPUT VOLTAGE - MAX | 500 V |

| | |
|--|---|
| OVERLOAD CURRENT IL AT 110% OVERLOAD | 17.6 A |
| OVERLOAD CURRENT IL AT 150% OVERLOAD | 18 A |
| SHOCK RESISTANCE | Mechanical, According to EN 61800-5-1, IEC/EN 60068-2-27 Storage and transportation: maximum 15 g, 11 ms (inside the packaging) UPS drop test (for weights inside the UPS frame) |
| SUITABLE FOR | Branch circuits, (UL/CSA) |
| SWITCHING FREQUENCY | 4 kHz, 1 - 12 kHz adjustable, fPWM, Power section, Main circuit |
| RATED OPERATIONAL VOLTAGE | 480 V AC, 3-phase 500 V AC, 3-phase 400 V AC, 3-phase |
| SHORT-CIRCUIT PROTECTION RATING | 20 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring |
| VIBRATION | Resistance: 5 - 15.8 Hz, Amplitude 1 mm (peak) Resistance: 15.8 - 150 Hz, 1 g, Maximum acceleration amplitude Resistance: 5 - 150 Hz, According to EN 61800-5-1, IEC/EN 60068-2-6 |
| RATED FREQUENCY - MAX | 66 Hz |
| RATED FREQUENCY - MIN | 45 Hz |
| RATED OPERATIONAL CURRENT (IE) AT 110% OVERLOAD | 16 A |
| RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD | 12 A |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 12 A |
| RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE | 5.5 kW |
| RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE, 110% OVERLOAD | 7.5 kW |

| | |
|---|--|
| RATED OPERATIONAL POWER AT 500 V, 50 HZ, 3-PHASE | 5.5 kW |
| SAFETY FUNCTION/LEVEL | STO (Safe Torque Off, SIL1, PLc Cat 1) |
| HEAT DISSIPATION AT CURRENT/SPEED | 100 W at 50% current and 50% speed 108 W at 50% current and 90% speed 155 W at 50% current and 0% speed 165 W at 100% current and 90% speed 66 W at 25% current and 0% speed 78 W at 100% current and 50% speed 83 W at 25% current and 50% speed 95 W at 100% current and 0% speed |

| |
|------------------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

