

Eaton 9E3000I

Eaton 9E UPS, 3000 VA, 2400W, Input: C20,
Output: (6) C13, (1) C19, Tower

PRODUCT NAME	Eaton 9E UPS
CATALOG NUMBER	9E3000I
UPC	786689166588
PRODUCT LENGTH/DEPTH	19 cm
PRODUCT HEIGHT	33 cm
PRODUCT WIDTH	39.9 cm
PRODUCT WEIGHT	24.2 kg
COMPLIANCES	CE Marked TUV
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 CE EAC

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Internal bypass allows service continuity in case of UPS fault
- LCD display for real-time status and measurements
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Long backup time with up to 4 optional EBM

TOPOLOGY	Online/Double-conversion
FORM FACTOR	Tower
CONSTRUCTION TYPE	Free standing model
COLOR	Black
VA RATING	3000 VA
WATTAGE	2400 W
RACK MOUNTING KIT	No

PACKAGE CONTENTS

- UPS
- USB cable
- Serial cable
- Quickstart guide
- Safety instructions

INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C20
INPUT NOMINAL VOLTAGE	230V default (220/230/240V)

NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(6) C13, (1) C19
NUMBER OF OUTPUTS C13	6
NUMBER OF OUTPUTS C19	1
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	• Automatic battery test • Deep discharge protection
BATTERY REPLACEMENT	Replacable batteries
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	13.5 min
COMMUNICATION	• USB port (HID compliant) • Serial port (RS232) • Communication slot
EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	LCD Display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	No

ALTITUDE	3000 m
BTU RATING	Online: 737
NOISE LEVEL	<37 dB at 1 meter
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	300 V
INPUT VOLTAGE - MIN	100 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	220 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	6
EFFICIENCY AT MAX. LOAD	91
EFFICIENCY (ECO-MODE)	97.5
INPUT VOLTAGE RANGE	176-300 V (100 V-300 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.8
OUTPUT VOLTAGE RANGE	220/230/240 V +/- 2%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	5 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3
POWER CONSUMPTION	237.4 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

