



## Eaton 9PX1000RT

Eaton 9PX UPS, 2U, 1000 VA, 900 W, 5-15P input, Outputs (8) 5-15R, 120V, Black/silver



<b>PRODUCT NAME</b>	Eaton 9PX UPS
<b>CATALOG NUMBER</b>	9PX1000RT
<b>UPC</b>	743172081254
<b>PRODUCT LENGTH/DEPTH</b>	17.7 in
<b>PRODUCT HEIGHT</b>	3.4 in
<b>PRODUCT WIDTH</b>	17.3 in
<b>PRODUCT WEIGHT</b>	36.4 lb
<b>COMPLIANCES</b>	IEC 62040-2 Cat C1 CISPR22 Class B FCC part 15 Class B VCCI Class B
<b>CERTIFICATIONS</b>	cULus Listed NOM



Powering Business Worldwide



<b>TOPOLOGY</b>	Online/Double-conversion
<b>RACK SIZE</b>	2U
<b>COLOR</b>	Black/silver
<b>VA RATING</b>	1000 VA
<b>WATTAGE</b>	900 W
<b>RACK MOUNTING KIT</b>	Yes

<b>PACKAGE CONTENTS</b>	<ul style="list-style-type: none"><li>• 1000VA 900W 120V 9PX Online Double-Conversion UPS with 8 Outlets</li><li>• USB cable</li><li>• RS-232 cable</li><li>• Rack-mounting hardware</li><li>• Tower support stands</li><li>• Safety guide</li><li>• Quick Start Guide</li></ul>
-------------------------	--

<b>INTERNAL BYPASS</b>	Yes
<b>INPUT CONNECTION</b>	<a href="#">5-15P</a>
<b>INPUT NOMINAL VOLTAGE</b>	120V default (100/110/120/125V)
<b>INPUT FREQUENCY RANGE</b>	60 Hz: 50-70 Hz, 50 Hz: 40-60 Hz
<b>INPUT POWER FACTOR</b>	>0.99 typical
<b>RECEPTACLE</b>	(8) 5-15R
<b>NUMBER OF OUTPUTS 5-15R</b>	8
<b>OUTPUT WAVEFORM</b>	True sine wave
<b>VOLTAGE</b>	120V
<b>OUTPUT NOMINAL VOLTAGE</b>	120V default (100/110/120/125V)
<b>RUNTIME GRAPH</b>	<code>\$row.attributeValue.cdata</code>
<b>BATTERY MANAGEMENT</b>	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
<b>BATTERY REPLACEMENT</b>	Hot-swappable internal batteries and extended battery modules (EBMs)
<b>BATTERY TYPE</b>	Sealed, lead-acid
<b>EXTENDED BATTERY CAPABILITY</b>	Add up to 4 extended battery modules (EBM). Part number 9PXEBM36RT
<b>STANDARD FACTORY WARRANTY</b>	<ul style="list-style-type: none"><li>• 3-YEAR FACTORY</li></ul>



---

WARRANTY

- - 3 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

**EXTENDED SERVICE PLANS**

- ADVANCED DEPOT EXCHANGE
- -5-year depot repair: 9SW5Y-1000UC
- -Expedited parts coverage for 5 years
- -Parts, electronics and UPS batteries coverage
- -Next business day shipping
- -Technical support
- 
- 5-YEAR ON-SITE PLAN: WFLN75XX-2509UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

**COMMUNICATION**

MiniSlot expansion port + 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote ON/OFF + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay  
Communication slot

**EXPANSION SLOTS**

- (1) Mini-Slot (MS) expansion port. Optional connectivity cards may be ordered separately.
- Gigabit Web/SNMP card part number:

	<p>NETWORK-M3</p> <ul style="list-style-type: none"> <li>• Modbus card part number: INDGW-M2</li> <li>• Relay card part number: RELAY-MS</li> </ul>
<b>SOFTWARE COMPATIBILITY</b>	Intelligent Power Software Suite
<b>USER INTERFACE</b>	Graphical display, 5-button programmable menu
<b>ALTITUDE</b>	0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)
<b>BTU RATING</b>	Online: 330, Battery: 646
<b>NOISE LEVEL</b>	<40 dB at 1 meter
<b>RELATIVE HUMIDITY</b>	0-96% non-condensing
<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
<b>PRODUCT HIGHLIGHTS</b>	<p>Keeps equipment running during outages to allow time for file saves and safe shutdown</p> <p>Optional NETWORK-M3 Gigabit network card enables full remote access and control</p> <p>NEMA 5-15R outlets split into separate switched banks for managed load shedding</p> <p>Interactive LCD interface keeps you updated on critical load information in real time</p> <p>Optional extended battery modules allow extended runtime to keep equipment powered</p>
<b>EFFICIENCY AT MAX. LOAD</b>	90.3%
<b>MAX NUMBER OF BATTERY PACKS</b>	4
<b>OUTPUT FREQUENCY</b>	50/60 Hz
<b>OUTPUT POWER FACTOR</b>	0.9
<b>OUTPUT VOLTAGE RANGE</b>	±1% steady-state
<b>RUNTIME AT FULL LOAD</b>	6 min

