



## Eaton 9PX11KG2

Eaton 9PX Gen 2 UPS, 11000 VA, 11000 W,  
Input: Hardwired, Outputs: Hardwired, (4)  
L6-30R, 4U Rack/tower, VRLA battery, Gigabit  
Network card included

□□□□

<b>PRODUCT NAME</b>	Eaton 9PX UPS
<b>CATALOG NUMBER</b>	9PX11KG2
<b>UPC</b>	786689860059
<b>PRODUCT LENGTH/DEPTH</b>	28.5 in
<b>PRODUCT HEIGHT</b>	6.85 in
<b>PRODUCT WIDTH</b>	17.32 in
<b>PRODUCT WEIGHT</b>	173.72 lb
<b>COMPLIANCES</b>	CISPR22 Class A / FCC part 15 Class A CE Marked FCC Part 15
<b>CERTIFICATIONS</b>	IEC 62040-2:2006 Cat C2 cULus Listed NOM ENERGY STAR certified ICC-ES AC156 OSHPD Seismic certified



Powering Business Worldwide

<b>SPECIAL FEATURES</b>	Gigabit Network Card (NETWORK-M3) included
<b>TOPOLOGY</b>	Online/Double-conversion
<b>RACK SIZE</b>	4U
<b>COLOR</b>	Black/silver
<b>VA RATING</b>	11 kVA
<b>WATTAGE</b>	11 kW
<b>RACK MOUNTING KIT</b>	Yes
<b>PACKAGE CONTENTS</b>	<ul style="list-style-type: none"> <li>• 11000VA 11000W 208V 9PX G2 Online Double-Conversion UPS</li> <li>• NETWORK-M3 Gigabit network card</li> <li>• USB cable</li> <li>• RS-232 cable</li> <li>• Cable gland for hardwire connection</li> <li>• Rack-mounting hardware</li> <li>• Tower support stands</li> <li>• Quick Start Guide</li> </ul>
<b>SURGE PROTECTION</b>	Yes
<b>INTERNAL BYPASS</b>	Yes
<b>INPUT CONNECTION</b>	Hardwired
<b>INPUT NOMINAL VOLTAGE</b>	208V default (200/208/220/230/240V)
<b>INPUT FREQUENCY RANGE</b>	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
<b>INPUT POWER FACTOR</b>	>0.99 typical
<b>RECEPTACLE</b>	(4) L6-30R, Hardwired
<b>NUMBER OF OUTPUTS L6-30R</b>	4
<b>OUTPUT WAVEFORM</b>	True sine wave
<b>VOLTAGE</b>	208 V
<b>OUTPUT NOMINAL VOLTAGE</b>	208V default (200/208/220/230/240/250V)
<b>RUNTIME GRAPH</b>	\$row.attributeValue.cdata
<b>BATTERY MANAGEMENT</b>	ABM+ technology uses battery replacement analytics to predict when you should replace UPS batteries based on real-life usage and conditions.
<b>BATTERY REPLACEMENT</b>	Hot-swappable internal batteries and extended battery modules (EBMs).

	Replacement battery part # EBP-2003 (qty 2 per UPS)
<b>BATTERY TYPE</b>	Sealed, lead-acid
<b>EXTENDED BATTERY CAPABILITY</b>	Add up to 12 EBMs, part # 9PXEBM240RTG2
<b>STANDARD FACTORY WARRANTY</b>	<ul style="list-style-type: none"> <li>• 3-YEAR FACTORY WARRANTY</li> <li>• - 3 years</li> <li>• - Parts, electronics and batteries coverage</li> <li>• - Standard ground shipping</li> <li>• - Technical support</li> </ul>
<b>EXTENDED SERVICE PLANS</b>	<ul style="list-style-type: none"> <li>• ADVANCED DEPOT EXCHANGE</li> <li>• - 5-year depot repair: 9SW5Y-11000UC</li> <li>• - Expedited parts coverage for 5 years</li> <li>• - Parts, electronics and UPS batteries coverage</li> <li>• - Next business day shipping</li> <li>• - Technical support</li> <li>•</li> <li>• 5-YEAR ON-SITE PLAN: WFLN75XX-11000UC</li> <li>• - On-site parts and labor coverage for years 5</li> <li>• - Parts, electronics and UPS batteries coverage</li> <li>• - 24x7 on-site labor coverage, next-day response</li> <li>• - Next-day shipping</li> <li>• - Technical support</li> </ul>
<b>RUNTIME AT HALF LOAD</b>	9.4 min
<b>EXPANSION SLOTS</b>	(2) Mini-Slot (MS) expansion ports with 1 Gigabit Network Card (NETWORK-M3) included
<b>ETHERNET INTERFACE</b>	Yes
<b>INCLUDES NETWORK CARD</b>	Yes
<b>SOFTWARE COMPATIBILITY</b>	Brightlayer Data Centers suite
<b>USER INTERFACE</b>	Graphical display, 5-button

	programmable menu, LED indicator
<b>ALTITUDE</b>	3000 m
<b>BTU RATING</b>	Online: 1160 BTU/hr, Battery: 1767 BTU/hr, High Efficiency: 188 BTU/hr
<b>NOISE LEVEL</b>	≤54 dB at 100% load, <38 dB at 66% load (at 1m, online mode, <87degrees F)
<b>RELATIVE HUMIDITY</b>	0-95% non-condensing
<b>TEMPERATURE RANGE</b>	0° to 40°C (32° to 104°F)
<b>PROTOCOL</b>	SNMP
<b>PRODUCT HIGHLIGHTS</b>	<p>Keeps equipment running during outages to allow time for file saves and safe shutdown</p> <p>Best-in-class efficiency results in reduced energy costs and greenhouse gas emissions</p> <p>Included NETWORK-M3 Gigabit network card enables full remote access and control</p> <p>Exclusive ABM+ technology and analytics help you pinpoint when to replace batteries</p> <p>Optional extended battery modules allow expanded runtime to keep equipment powered</p>
<b>EFFICIENCY AT MAX. LOAD</b>	97%
<b>MAX NUMBER OF BATTERY PACKS</b>	12
<b>OUTPUT FREQUENCY</b>	50/60 Hz
<b>OUTPUT POWER FACTOR</b>	1.0
<b>OUTPUT VOLTAGE RANGE</b>	±1% steady-state
<b>RUNTIME AT FULL LOAD</b>	3.1 min. (11000W)

