


Eaton 9PX1500GRT

Eaton 9PX UPS, 2U, 1500 VA, 1350 W, C14 input, Outputs: (8) C13, 208V

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX1500GRT
UPC	743172081346
PRODUCT LENGTH/DEPTH	17.7 in
PRODUCT HEIGHT	3.4 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	41.4 lb
COMPLIANCES	IEC 62040-2 Class B Cat C2
	CISPR22 Class B
	FCC part 15 Class B
	CE Marked
CERTIFICATIONS	cULus Listed ENERGY STAR certified

TOPOLOGY	Online/Double-conversion
FORM FACTOR	Rack/tower
RACK SIZE	2U
COLOR	Black/silver
VA RATING	1500 VA
WATTAGE	1350 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	<ul style="list-style-type: none">• 9PX1500GRT UPS• 4-post rail kit• Safety manual• User manual• Tower pedestals• RS-232 serial cable• USB cable• Intelligent Power Software Suite CD
INTERNAL BYPASS	Yes
INPUT CONNECTION	C14
INPUT CORD LENGTH	6 ft
INPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
INPUT FREQUENCY RANGE	60 Hz: 50–70 Hz, 50 Hz: 40–60 Hz
INPUT POWER FACTOR	>0.99 typical
RECEPTACLE	(8) C13
NUMBER OF OUTPUTS C13	8
OUTPUT WAVEFORM	True sine wave
VOLTAGE	208 V
OUTPUT NOMINAL VOLTAGE	208V default (200/208/220/230/240/250V)
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	ABM technology (3-stage charging extends battery service life by 50% and provides advance warning for battery replacement)
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Add up to 4 extended battery modules (EBM). Part number 9PXEBM48RT



STANDARD FACTORY WARRANTY

- 3-YEAR FACTORY WARRANTY
- - 3 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

EXTENDED SERVICE PLANS

- ADVANCED DEPOT EXCHANGE
- - 5-year depot repair: 9SW5Y-1500UC
- - Expedited parts coverage for 5 years
- - Parts, electronics and UPS batteries coverage
- - Next business day shipping
- - Technical support
-
- 5-YEAR ON-SITE PLAN: WFLN75XX-2509UC
- - On-site parts and labor coverage for years 5
- - Parts, electronics and UPS batteries coverage
- - 24x7 on-site labor coverage, next-day response
- - Next-day shipping
- - Technical support

COMMUNICATION

MiniSlot + 1 USB port + 1 serial RS232 port + 1 mini-terminal block for remote ON/OFF + 1 mini-terminal block for remote power off + 1 mini-terminal block for output relay
Communication slot

EXPANSION SLOTS

- (1) Mini-Slot (MS) expansion port. The following optional connectivity cards may be ordered separately.
 - Gigabit Network
-

	Card part number: NETWORK-M3 <ul style="list-style-type: none">• Modbus card part number: INDGW-M2• Relay card part number: RELAY-MS
SOFTWARE COMPATIBILITY	Intelligent Power Software Suite
USER INTERFACE	Graphical display, 5-button programmable menu
ALTITUDE	0-1500m (0° to 40°C), 1500-3000m (0° to 35°C)
BTU RATING	Online: 494, Battery: 731
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
EFFICIENCY AT MAX. LOAD	91.2%
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT VOLTAGE RANGE	±1% steady-state
RUNTIME AT FULL LOAD	5 min

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

