

Eaton 60LR85

Eaton Bussmann series low voltage british standard fuse, 60A, AC 415 V, system C type II, 23 x 57 mm, gL/gG, 4.5W Loss

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	60LR85
PRODUCT LENGTH/DEPTH	56 mm
PRODUCT HEIGHT	31 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	100.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269

AMPERAGE RATING	60 A
CURRENT TYPE	AC
BREAKING CAPACITY	33 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	LR85
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
FUSE INDICATOR	Other
WATT LOSSES	4.5 W
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION	BS system C type II
CONSTRUCTION SIZE	23 x 57 mm
FUSE SHAPE	Cylindrical
VOLTAGE TYPE	AC
MATERIAL	Ceramic
RELEASE CHARACTERISTIC	Other
VOLTAGE RATING	415 V
TYPE	fuse
APPLICATION	protection of incoming cables into residential and commercial properties

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250979en.pdf
-----------------------------------	--



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.