



□□□□□

Eaton 63AFE

Fuse-link, high speed, 63 A, AC 690 V, DC 500 V, BS88, 18 x 96 mm, aR, BS

□□□□

PRODUCT NAME	Eaton Bussmann series high speed british standard fuse
CATALOG NUMBER	63AFE
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	22 mm
PRODUCT WIDTH	187 mm
PRODUCT WEIGHT	45.8 g
COMPLIANCES	CE

□□□□

□□

AMPERAGE RATING	63 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
RATED SWITCHING CAPACITY	200 kA
RATED VOLTAGE AC	690 V
RATED VOLTAGE DC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76 mm
MOUNTING DIMENSION	M8
CURRENT TYPE	AC/DC
CLASS	Class aR
WATT LOSSES	18.5 W
FUSE SHAPE	Offset slotted bolted tags
COLOR	None
CONSTRUCTION SIZE	Other
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	AFE
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

