

Eaton 63MJ31-8

Eaton Bussmann series low voltage british standard fuse, 63A, AC 415 V, V88/J, 31 x 131 mm, gU, type 8

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	63MJ31-8
UPC	051712516600
PRODUCT LENGTH/DEPTH	160 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	231.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC

AMPERAGE RATING	63 A
FITTED WITH:	Slotted tags
CURRENT TYPE	AC
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	MJ31
UTILIZATION CATEGORY	gU (utility/distribution protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	5 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/J
CONSTRUCTION SIZE	J
FUSE SHAPE	Dual slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	feeder pillars
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk251033en.pdf](#)



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

