



Eaton 9PX3000IRT2U-L

Eaton 9PX UPS, Lithium, 3000 VA, 3000 W,
Input: C20, Outputs: (8) C13, (2) C19,
Rack/tower, 2U

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX3000IRT2U-L
UPC	743172105325
PRODUCT LENGTH/DEPTH	605 mm
PRODUCT HEIGHT	86.5 mm
PRODUCT WIDTH	440 mm
PRODUCT WEIGHT	22.8 kg
COMPLIANCES	CE Marked

SPECIAL FEATURES

- Lithium-ion batteries
- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Energy Star qualified, provides the highest efficiency level to reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (down to the managed outlet groups)
- Long backup time with up to 4 optional EBM

TOPOLOGY	Online/Double-conversion
RACK SIZE	2U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	3000 VA
WATTAGE	3000 W
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS

- UPS
 - Input cable
 - (2) IEC-IEC output cables
 - USB cable
 - Serial cable
 - (2) brackets for 19" mounting
 - (2) Rack-mounting kit
-

- (2) Supports for tower mounting
- Cable locking system
- Safety instructions
- Quickstart guide

INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C20
INPUT CORD LENGTH	1.8m
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13, (2) C19
NUMBER OF OUTPUT CONNECTIONS FRENCH STANDARD (TYPE E)	0
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	2
NUMBER OF OUTPUTS HARDWIRED	0
NUM OF OUTPUTS PC (SCHUKO)	0
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata

BATTERY MANAGEMENT

- Lithium-ion batteries with battery management system
- Automatic

	recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY TYPE	Lithium-ion
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	20.5 min
COMMUNICATION	• USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Mini-terminal block for output relay • Dry contacts (3 outputs, 1 input, optocoupler, DB9)
EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 614
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	100 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz

SECONDARY FREQUENCY - MIN	50 Hz
EFFICIENCY AT MAX. LOAD	94
EFFICIENCY (ECO-MODE)	98
INPUT VOLTAGE RANGE	176-276 V (100-276 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 1%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	10 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3
POWER CONSUMPTION	180 W
