



## Eaton 63NHG02B-400

Fuse-link, LV, 63 A, AC 400 V, NH02, gL/gG, IEC, dual indicator, live gripping lugs



<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage NH Fuse
<b>CATALOG NUMBER</b>	63NHG02B-400
<b>PRODUCT LENGTH/DEPTH</b>	150 mm
<b>PRODUCT HEIGHT</b>	63 mm
<b>PRODUCT WIDTH</b>	40 mm
<b>PRODUCT WEIGHT</b>	427 g
<b>COMPLIANCES</b>	RoHS Compliant CE Marked
<b>CERTIFICATIONS</b>	IEC 60269-1 IEC 60269-2 DIN 43620



Powering Business Worldwide



<b>AMPERAGE RATING</b>	63 A
<b>FITTED WITH:</b>	Metal gripping lugs
<b>FUSE SIZE</b>	NH02
<b>CURRENT TYPE</b>	AC
<b>BREAKING CAPACITY</b>	120 kA
<b>FREQUENCY RATING - MAX</b>	62 Hz
<b>FREQUENCY RATING - MIN</b>	45 Hz
<b>RATED SWITCHING CAPACITY</b>	120 kA
<b>RATED VOLTAGE AC</b>	400 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	Square body with knife blade contact
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>INTERRUPT RATING</b>	120 kAIC
<b>FUSE INDICATOR</b>	Combination fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	5.5 W
<b>CONNECTION</b>	Blade end
<b>CONSTRUCTION</b>	NH02
<b>CONSTRUCTION SIZE</b>	NH02
<b>FUSE SHAPE</b>	Square body Knife blade contacts
<b>VOLTAGE TYPE</b>	AC
<b>SUITABLE FOR</b>	Microswitch BVL50
<b>MATERIAL</b>	Ceramic body
<b>QUANTITY</b>	3
<b>VOLTAGE RATING</b>	400 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	<ul style="list-style-type: none"><li>• industrial</li><li>• Utilities, Solar, Wind</li></ul>
<b>RATED SWITCHING CAPACITY AC</b>	120 kA



DECLARATIONS OF CONFORMITY

[eaton-low-voltage-nh-fuse-declaration-of-conformity-uk250967en.pdf](#)

