

## Eaton 63NHG02BI

Fuse-link, LV, 63 A, AC 500 V, NH02, gL/gG, IEC, dual indicator, insulated gripping lugs


|                         |                                              |
|-------------------------|----------------------------------------------|
|                         |                                              |
| PRODUCT NAME            | Eaton Bussmann series<br>low voltage NH Fuse |
| CATALOG NUMBER          | 63NHG02BI                                    |
| PRODUCT<br>LENGTH/DEPTH | 150 mm                                       |
| PRODUCT HEIGHT          | 63 mm                                        |
| PRODUCT WIDTH           | 39 mm                                        |
| PRODUCT WEIGHT          | 0.408 kg                                     |
| COMPLIANCES             | CE Marked<br>RoHS Compliant                  |
| CERTIFICATIONS          | IEC 60269-1<br>IEC 60269-2<br>DIN 43620      |



|                                      |                                               |
|--------------------------------------|-----------------------------------------------|
| AMPERAGE RATING                      | 63 A                                          |
| FITTED WITH:                         | Insulated metal gripping lugs                 |
| FUSE SIZE                            | NH02                                          |
| CURRENT TYPE                         | AC                                            |
| BREAKING CAPACITY                    | 120 kA                                        |
| RATED SWITCHING CAPACITY             | 120 kA                                        |
| RATED VOLTAGE AC                     | 500 V                                         |
| CLASS                                | Class gG/gL                                   |
| FUSE TYPE                            | Square body with knife blade contact          |
| UTILIZATION CATEGORY                 | gL/gG (cable protection/equipment protection) |
| INTERRUPT RATING                     | 120 kAIC                                      |
| FUSE INDICATOR                       | Combination fuse status indicator             |
| INSULATED METAL GRIPPING LUGS (IMGL) | Yes                                           |
| WATT LOSSES                          | 5.5 W                                         |
| CONNECTION                           | Blade end                                     |
| CONSTRUCTION                         | NH02                                          |
| CONSTRUCTION SIZE                    | NH02                                          |
| FUSE SHAPE                           | Square body<br>Knife blade contacts           |
| VOLTAGE TYPE                         | AC                                            |
| SUITABLE FOR                         | Microswitch BVL50                             |
| MATERIAL                             | Ceramic body                                  |
| QUANTITY                             | 3                                             |
| VOLTAGE RATING                       | 500 V                                         |
| TYPE                                 | Fuse                                          |

|             |                                                                                               |
|-------------|-----------------------------------------------------------------------------------------------|
| APPLICATION | <ul style="list-style-type: none"><li>• industrial</li><li>• Utilities, Solar, Wind</li></ul> |
|-------------|-----------------------------------------------------------------------------------------------|

|                             |        |
|-----------------------------|--------|
| RATED SWITCHING CAPACITY AC | 120 kA |
|-----------------------------|--------|



|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

