

Eaton 9PX3000IRTBPF

Eaton 9PX UPS HotSwap FR, 3000 VA, 3000 W, Input: C20, Outputs: (4) French, (1) C19, Rack/tower, 3U

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX3000IRTBPF
UPC	743172081506
PRODUCT LENGTH/DEPTH	48.5 cm
PRODUCT HEIGHT	13 cm
PRODUCT WIDTH	44 cm
PRODUCT WEIGHT	30 kg
COMPLIANCES	CE Marked TUV cULus Listed CSA 22.2 FCC part 15 Class B CISPR22 Class B
CERTIFICATIONS	EAC CE ENERGY STAR certified IEC/EN 62040-1 UL 1778 IEC/EN 62040-2

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- First UPS in its class to provide Unity power factor (VA=W)
- Energy Star qualified, provides the highest efficiency level to reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (down to the managed outlet groups)
- Hot swappable batteries
- Advanced Battery Management (ABM) technology to increase battery lifetime
- Long backup time with up to 4 optional EBM

TOPOLOGY	Online/Double-conversion
FORM FACTOR	Rack/tower
RACK SIZE	3U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	3000 VA

WATTAGE	3000 W
RACK MOUNTING KIT	Yes
PACKAGE CONTENTS	• UPS • Input cable • Maintenance Bypass • (2) IEC-IEC output cables • USB cable • Serial cable • (2) brackets for 19" mounting • (2) Rack-mounting kit • (2) Supports for tower mounting • Cable locking system • Safety instructions • Quickstart guide
INTERNAL BYPASS	Yes
HOT SWAP POWER	Yes
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	C20
INPUT CORD LENGTH	1.8m
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(4) French, (1) C19
NUMBER OF OUTPUTS C19	1
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata

BATTERY MANAGEMENT	• ABM & Temperature compensated charging method (user selectable) • Automatic battery test • Deep discharge protection • Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	9.5 min
COMMUNICATION	• USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Mini-terminal block for output relay • Dry contacts (3 outputs, 1 input, optocoupler, DB9)
EXPANSION SLOTS	One slot for optional communication card
ETHERNET INTERFACE	No
INCLUDES NETWORK CARD	No
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m

BTU RATING	Online: 614
NOISE LEVEL	<40 dB at 1 meter
RELATIVE HUMIDITY	0-96% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
INPUT VOLTAGE - MAX	276 V
INPUT VOLTAGE - MIN	100 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	6
EFFICIENCY AT MAX. LOAD	94
EFFICIENCY (ECO-MODE)	98
INPUT VOLTAGE RANGE	176-276 V (100-276 V with derating)
MAX NUMBER OF BATTERY PACKS	4
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	1
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 1%
PHASE (INPUT)	1
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	3 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	3
POWER CONSUMPTION	180 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

