



Eaton 9PX3000RT-L

Eaton 9PX lithium ion UPS, 2U, 3000 VA, 2700 W, L5-30P input, Outputs: (6) 5-20R, (1) L5-30R, 120 V

□□□□

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton 9PX UPS |
| CATALOG NUMBER | 9PX3000RT-L |
| UPC | 743172105387 |
| PRODUCT LENGTH/DEPTH | 23.82 in |
| PRODUCT HEIGHT | 3.41 in |
| PRODUCT WIDTH | 17.32 in |
| PRODUCT WEIGHT | 52.8 lb |
| COMPLIANCES | FCC part 15 Class B IEC 62040-2 Cat C1 |
| CERTIFICATIONS | cULus Listed NOM ICC-ES AC156 OSHPD Seismic certified |



Powering Business Worldwide



| | |
|--------------------------|--------------------------|
| TOPOLOGY | Online/Double-conversion |
| RACK SIZE | 2U |
| COLOR | Black/silver |
| VA RATING | 3000 VA |
| WATTAGE | 2700 W |
| RACK MOUNTING KIT | Yes |

| | |
|-------------------------|---|
| PACKAGE CONTENTS | <ul style="list-style-type: none">• 3000VA 2700W 120V 9PX Online Double-Conversion UPS with 7 Outlets• USB cable• RS-232 cable• Rack-mounting hardware• Tower support stands• Safety guide• Quick Start Guide |
|-------------------------|---|

| | |
|---------------------------------|--|
| INTERNAL BYPASS | Yes |
| INPUT CONNECTION | L5-30P |
| INPUT CORD LENGTH | 8 ft |
| INPUT NOMINAL VOLTAGE | 120V default (100/110/120/125V) |
| INPUT FREQUENCY RANGE | 60 Hz: 50-70 Hz, 50 Hz: 40-60 Hz |
| INPUT POWER FACTOR | >0.99 typical |
| RECEPTACLE | (6) 5-20R, (1) L5-30R, 120V |
| NUMBER OF OUTPUTS 5-20R | 6 |
| NUMBER OF OUTPUTS L5-30R | 1 |
| OUTPUT WAVEFORM | True sine wave |
| VOLTAGE | 120V |
| OUTPUT NOMINAL VOLTAGE | 120V default (100/110/120/125V) |
| RUNTIME GRAPH | \$row.attributeValue.cdata |
| BATTERY MANAGEMENT | Integrated battery management system (BMS) for temperature regulation and life cycle monitoring |
| BATTERY REPLACEMENT | Hot-swappable internal batteries and extended battery modules (EBMs). Replacement battery part # EBP-1609-L (qty 1 per UPS). |



| | |
|------------------------------------|--|
| BATTERY TYPE | Lithium-ion |
| EXTENDED BATTERY CAPABILITY | Add up to 4 extended battery modules (EBM). Part number 9PXEBM72RT-L |
| STANDARD FACTORY WARRANTY | <ul style="list-style-type: none"> • 5-YEAR FACTORY WARRANTY • - 5 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support |
| BATTERY CHEMISTRY | Lithium Iron Phosphate (LiFePo4) |
| COMMUNICATION | RS-232 (RJ45) ports; USB port as standard (HID). 6-foot RS-232 and USB cables included |
| EXPANSION SLOTS | <ul style="list-style-type: none"> • (1) Mini-Slot (MS) expansion port. The following optional connectivity cards may be ordered separately. • Gigabit Network Card part number: NETWORK-M3 • Modbus card part number: INDGW-M2 • Relay card part number: RELAY-MS |
| SOFTWARE COMPATIBILITY | Intelligent Power Software Suite |
| USER INTERFACE | Graphical display, 5-button programmable menu |
| ALTITUDE | 0-1500m (0° to 40°C), 1500-3000m (0° to 35°C) |
| BTU RATING | Online: 844, Battery: 1462 |
| NOISE LEVEL | <47 dB at 1 meter |
| RELATIVE HUMIDITY | 0-96% non-condensing |
| TEMPERATURE RANGE | 0° to 40°C (32° to 104°F) |
| PRODUCT HIGHLIGHTS | Keeps equipment running during outages to allow time for file saves and safe shutdown Improved lithium-ion batteries have service life |

