



□□□□

Eaton 9PX5KIRTN

Eaton 9PX UPS Netpack, 5000 VA, 4500 W, Input: Hardwired, Outputs: (8) C13, (2) C19, Hardwired, Rack/tower, 3U, Network card included

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX5KIRTN
PRODUCT LENGTH/DEPTH	68.5 cm
PRODUCT HEIGHT	13 cm
PRODUCT WIDTH	44 cm
PRODUCT WEIGHT	48 kg
COMPLIANCES	CE Marked TUV cULus Listed CSA 22.2
CERTIFICATIONS	UL 1778 IEC/EN 62040-1 IEC/EN 62040-2 CE EAC



Powering Business Worldwide

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Provides more real power (watts) to protect more equipment with a 0.9 power factor
- Energy Star qualified, provides the highest efficiency level to reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Network card and rackmounting kit delivered as standard
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (at the UPS level)
- Parallel operation using HotSync technology
- Hot swappable batteries

TOPOLOGY	Online/Double-conversion
RACK SIZE	3U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	5000 VA
WATTAGE	4500 W
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS	<ul style="list-style-type: none"> • UPS • (2) IEC-IEC output cables
-------------------------	--

- Network Management Card
- USB cable
- Serial cable
- (2) Supports for tower mounting
- (2) brackets for 19" mounting
- (2) Rack-mounting kit
- Cable locking system
- Safety instructions
- Quickstart guide

INTERNAL BYPASS	Yes
HOT SWAP POWER	No
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	Hardwired/fixed connection
INPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(8) C13, (2) C19, Hardwired
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	2
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	Sine wave
VOLTAGE	230V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	1
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata
BATTERY MANAGEMENT	<ul style="list-style-type: none"> • ABM & Temperature compensated charging method

	<ul style="list-style-type: none"> (user selectable) • Automatic battery test • Deep discharge protection • Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable internal batteries and extended battery modules (EBMs)
BATTERY RATING	12 V / 5 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	\$row.attributeValue.cdata
RUNTIME AT HALF LOAD	11 min
COMMUNICATION	<ul style="list-style-type: none"> • USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Dry contacts (4 outputs, relay, DB9) • DB15 for parallel operation • Network card
EXPANSION SLOTS	One slot, network card included
ETHERNET INTERFACE	Yes
INCLUDES NETWORK CARD	Yes
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 922
NOISE LEVEL	<45 dB at 1 meter
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
PROTOCOL	SNMP

