



□□□□□

Eaton 9PX6KIRTNBP31

Eaton 9PX UPS 3:1 HotSwap Netpack, 6000 VA, 5400 W, Input: Hardwired, Outputs: (4) C19, Hardwired, Rack/tower, 6U, Network card included

□□□□

PRODUCT NAME	Eaton 9PX UPS
CATALOG NUMBER	9PX6KIRTNBP31
UPC	743172045256
PRODUCT LENGTH/DEPTH	70 cm
PRODUCT HEIGHT	26 cm
PRODUCT WIDTH	44 cm
PRODUCT WEIGHT	88 kg
COMPLIANCES	CE Marked TUV
CERTIFICATIONS	IEC/EN 62040-1 IEC/EN 62040-2 CE EAC

SPECIAL FEATURES

- Double conversion topology
- Constantly monitors power conditions and regulates voltage and frequency
- Provides more real power (watts) to protect more equipment with a 0.9 power factor
- Energy efficient, reduce energy and cooling costs
- Internal bypass allows service continuity in case of UPS fault
- Next-generation graphical LCD display
- Network card and rackmounting kit delivered as standard
- Compatible with Virtual environments (VMware, Hyper-V, Citrix Xen, Redhat)
- Meter energy consumption (at the UPS level)
- Parallel operation using HotSync technology
- Hot swappable batteries

TOPOLOGY	Online/Double-conversion
RACK SIZE	6U
CONSTRUCTION TYPE	482.6 mm (19 inch) device
COLOR	Black/silver
VA RATING	6000 VA
WATTAGE	5400 W
RACK MOUNTING KIT	Yes

PACKAGE CONTENTS

- Power Module
- Extended battery module (EBM)
- Maintenance Bypass
- Network

- Management Card
- (2) brackets for 19' mounting
- (2) Rack-mounting kit
- USB cable
- Serial cable
- Battery cable with comms for automatic battery cabinet recognition
- (2) Supports for tower mounting
- Link plate
- Safety instructions
- Quickstart guide

INTERNAL BYPASS	Yes
HOT SWAP POWER	Yes
AUTO SHUTDOWN FUNCTION	Yes
PRIMARY FREQUENCY - MAX	70 Hz
PRIMARY FREQUENCY - MIN	40 Hz
INPUT CONNECTION	Hardwired/fixed connection
INPUT NOMINAL VOLTAGE	400V default (380/400/415V)
NOMINAL FREQUENCY	50/60 Hz
INPUT FREQUENCY RANGE	40-70 Hz
INPUT POWER FACTOR	>.99
RECEPTACLE	(4) C19, Hardwired
NUMBER OF OUTPUTS C19	4
NUMBER OF OUTPUTS HARDWIRED	1
OUTPUT WAVEFORM	Sine wave
VOLTAGE	400V
OUTPUT NOMINAL VOLTAGE	230V default (200/208/220/230/240V)
FEED TYPE	2
VOLTAGE TYPE	AC
RUNTIME GRAPH	\$row.attributeValue.cdata

- | | |
|---------------------------|---|
| BATTERY MANAGEMENT | <ul style="list-style-type: none"> • ABM & Temperature compensated charging method |
|---------------------------|---|

	(user selectable) • Automatic battery test • Deep discharge protection • Automatic recognition of external battery units
BATTERY REPLACEMENT	Hot-swappable battery modules
BATTERY RATING	12 V / 9 Ah
BATTERY TYPE	Sealed, lead-acid
EXTENDED BATTERY CAPABILITY	Yes
RUNTIME AT HALF LOAD	21 min
COMMUNICATION	• USB port (HID compliant) • Serial port (RS232) • Mini terminal block for remote On/Off • Mini-terminal block for remote power off • Dry contacts (4 outputs, relay, DB9) • Network card
EXPANSION SLOTS	One slot, network card included
ETHERNET INTERFACE	Yes
INCLUDES NETWORK CARD	Yes
SOFTWARE COMPATIBILITY	Eaton Intelligent Power Manager, Eaton Intelligent Power Protector
USER INTERFACE	Multilingual graphical LCD display
TYPE OF INTERFACE	Other
POTENTIAL FREE SWITCH CONTACT	Yes
ALTITUDE	3000 m
BTU RATING	Online: 1105
NOISE LEVEL	<48 dB at 1 meter
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
PROTOCOL	SNMP
INTEGRATED FUNCTIONALITY	Network Mangement

INPUT VOLTAGE - MAX	305 V
INPUT VOLTAGE - MIN	480 V
OUTPUT VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MIN	200 V
SECONDARY FREQUENCY - MAX	60 Hz
SECONDARY FREQUENCY - MIN	50 Hz
BATTERY QUANTITY	20
EFFICIENCY AT MAX. LOAD	94
EFFICIENCY (ECO-MODE)	98
INPUT VOLTAGE RANGE	305-480 V
MAX NUMBER OF BATTERY PACKS	12 (supercharger required for more than 6 EBM)
OUTPUT FREQUENCY	50/60 Hz
OUTPUT POWER FACTOR	0.9
OUTPUT VOLTAGE RANGE	200/208/220/230/240 V +/- 1%
PHASE (INPUT)	3
PHASE (OUTPUT)	1
RUNTIME AT FULL LOAD	8 min
VOLTAGE DISTORTION OUTPUT (LINEAR LOAD) - MAX	2
POWER CONSUMPTION	324 W

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton Ireland

